

## Mini DVI to DVI Cable Adapter, Video Converter for Macbooks and iMacs, 1920x1200 (Mini DVI to DVI-D M/F)

MODEL NUMBER: **P138-000-DVI**



### Highlights

- Connect a DVI Monitor to Apple Intel iMac, MacBook, and 12in PowerBook G4 mini-DVI Port
- 8 in. overall length
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### System Requirements

- Apple Intel iMac, MacBook, and 12in PowerBook G4

### Package Includes

- 8-in. mini-DVI to DVI-D Adapter

### Description

Tripp Lite's mini-DVI to DVI-D Digital Female Video Adapter Cable allows you to connect a DVI-D Display to the mini-DVI port found on some Apple computer models. Supports Single Link digital transmission, with resolutions up to 1920x1200@60Hz.

### Features

- Connect a DVI Monitor to Apple Intel iMac, MacBook, and 12-in. PowerBook G4 mini-DVI Port
- 8 in. overall length
- 1920x1200 @ 60Hz resolution
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
Display Style	Adapter
Cable Type	DVI
INPUT	
Cable Length (ft.)	0.7
Cable Length (m)	0.21
Cable Length (in.)	8
PHYSICAL	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Color	White
<b>CONNECTIONS</b>	
Connector A	MINI-DVI (MALE)
Connector B	DVI-D DUAL LINK (FEMALE)
<b>SPECIAL FEATURES</b>	
Chromebook Compatible	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>