

## SATA to eSATA Transition Cable (7Pin/7Pin), 3-ft.

MODEL NUMBER: P952-003



### Highlights

- SATA Internal "L" to External eSATA "I" Cable - 3-ft.
- Supports data transfer rates of up to 6.0 Gbps
- Cable is shielded to protect against EMI/RFI line noise

### Package Includes

- SATA to eSATA Transition Cable - 3-ft.

### Description

Tripp Lite's SATA to eSATA Transition Cable allows new eSATA devices to be connected to older style SATA ports. Cable is optimized for data storage with up to 6 Gbps transfer rate.

### Features

- SATA Internal "L" to External eSATA "I" Data Cable - 3-ft.
- Supports data transfer rates up to 6 Gbps
- Fully shielded cable to protect against EMI/RFI line noise

## Specifications

OVERVIEW	
Cable Type	SATA
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.91
PHYSICAL	
Color	Red
CONNECTIONS	
Connector A	7 PIN SATA (MALE)
Connector B	7 PIN ESATA (MALE)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>