

USB 3.0 SuperSpeed to Serial ATA (SATA) and IDE Adapter for 2.5in or 3.5in Hard Drives

MODEL NUMBER: U338-000



Description

Tripp Lite's U338-000 USB 3.0 to SATA / IDE Adapter provides individual or simultaneous connection to either a Serial ATA or IDE drive (2.5" / 3.5" / 5.25") to allow you to configure hard drives without having to install them first. With transfer speeds up to 6 Gbps (w/ SATA III), the U338-000 provides a fast, convenient way to format hard drives or transfer files. You can also transfer data between a SATA and an IDE drive over the adapter. The unit features both 2.5" IDE (44-pin) and 3.5" (40-pin) connections, and a 22-Pin SATA Data + Power connector. It works with any SATA and certain IDE drives. See Compatibility List. Windows-compatible AI-OTB One Touch Backup software is included to allow you to quickly backup and restore files. The U338-000 is compatible with Windows and Mac. The U338-000 is manufactured using top-quality materials to ensure error-free data transmission and hard drive formatting.

Features

- USB 3.0 and below compliant
- SATA III (6Gbps) and below compliant
- Supports Plug-and-Play
- USB Mass Storage Class Bulk-Only Transport specification
- 40-pin and 44-pin IDE connectors, and a 22-Pin SATA Data + Power connector
- Compatible with 2.5" / 3.5" / 5.25" SATA and IDE drives
- Supports drives up to 4TB
- Includes AI-OTB One Touch Backup software, and features a button for one touch backup
- Compatible with Windows and Mac

Specifications

OVERVIEW

Highlights

- Formats hard drives, enables file transfers, or works as external storage device
- SuperSpeed (5Gbps) / Hi-Speed (480 Mbps) / Full-Speed (12 Mbps) Compliant
- SATA III (6Gbps) / SATA Gen2i (3Gbps) / Gen1i (1.5Gbps) Compliant
- Compatible with 2.5" / 3.5" / 5.25" SATA and IDE drives
- Supports drives up to 4TB
- Includes AI-OTB One Touch Backup software, and features a button for one touch backup
- Compatible with Windows and Mac

Applications

- Formatting hard drives, File Transfers, or External Storage

System Requirements

- 2.5" / 3.5" / 5.25" SATA and/or IDE drive
- Supports drives up to 4TB
- Computer with an available USB port. A USB 3.0 port is required to reach maximum speeds.
- AI-OTB software compatible with Windows
- U338-000 compatible with Windows and Mac

Product Versions and Backup Software

A new version of the U338-000 was released in 2014, and it uses AI-OTB One Touch Backup software, instead of the PC Clone Ex Lite software used by the original version. In the Support tab on this web page you will find zip folders for both versions of the backup software. In addition to including the



Cable Type	USB
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	USB 3.0 MICRO-B (FEMALE)
Connector B	22 PIN SATA + POWER (FEMALE)
Connector C	40 POS. SOCKET (FEMALE)
SPECIAL FEATURES	
Chromebook Compatible	Yes
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

software. In addition to including the applicable driver, they contain a Release Notes file that will tell you how to determine which version you have, and therefore, which backup software you need to use. Both versions of the U338-000 function the same, with the only difference being the Backup software they use.

Package Includes

- USB 3.0 to SATA / IDE Adapter
- USB 3.0 Cable – Micro B Male to A Male (2.5 ft)
- 4-Pin Molex Power Cable (4-inch)
- External Power Supply (Input: 100-240V, 50/60Hz, 0.8A, 5-ft cord; Output: 12V, 2A)
- Backup Software CD
- Owner's Manual

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>