

## Duplex Multimode 62.5/125 LSZH Fiber Optic Cable, 1000-ft. Bulk

MODEL NUMBER: N549-01K



### Highlights

- Bulk 62.5/125 Multimode Duplex Fiber Optic Cable
- Low-Smoke, Zero Halogen (LSZH) jacket
- Zip-Cord Style

### Package Includes

Carton of 1,000ft Duplex 62.5/125 Multimode cable

### Description

Tripp Lite N549-01K bulk 62.5/125 multimode fiber optic cable is ideal for long backbone runs, or for making your own Fiber patch cables. Individual fibers surrounded by Kevlar yarn for maximum tensile strength and protection. Low-Smoke, Zero Halogen (LSZH) jacket.

### Features

- Bulk 62.5/125 Multimode Duplex Fiber Optic Cable
- Low-Smoke, Zero Halogen jacket
- Zip-Cord Style
- Cable marked every meter
- Temp Range: -20C to +70C
- Suitable for Indoor Use
- 7lb Reel

## Specifications

OVERVIEW	
Clad Diameter	125mu
Core Diameter	62.5mu
Number of Fibers	2
Shipping Weight	7lb
Fiber Type	62.5/125 - OM1
Cable Type	Multimode; Bulk



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.triplite.com

<b>INPUT</b>	
Cable Length (ft.)	1000
Cable Length (m)	304.8
<b>PHYSICAL</b>	
Color	Orange
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-20C to +70C
<b>COMMUNICATIONS</b>	
Network Speed	1Gbps
<b>CONNECTIONS</b>	
Connector A	62.5 BULK
Connector B	62.5 BULK
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.triplite.com/products/product-certification-agencies>