

Type N Coaxial Connectors, 50 Ohm

Item #	Description	Cable Type	Attachment	1-9	10-24	25-99	100+
ANM-1A18	Type N Male	RG6	Crimp	4.10	3.77	3.44	CALL
BAC536	Type N Male	RG142/RG223/RG400	Crimp	6.46	6.07	5.68	CALL
BAC523	Type N Male	RG174	Crimp	7.93	7.45	6.98	CALL
BAN111	Type N Male	RG213	Clamp	7.35	6.91	6.47	CALL
BAC506	Type N Male	RG213	Crimp	7.04	6.62	6.20	CALL
ANM-1J00	Type N Male, Right Angle	RG142/RG223/RG400	Crimp	7.93	7.45	6.98	CALL
ANM-1114	Type N Male	RG316/RG174/RG188	Crimp	4.10	3.77	3.44	CALL
ANM-1700	Type N Male	Low Loss 195-Series, RG58	Crimp	4.10	3.77	3.44	CALL
ANM-1716	Type N Male, Right Angle	Low Loss 195-Series, RG58	Crimp	4.94	4.54	4.15	CALL
ANM-1202	Type N Male	Low Loss 200-Series	Crimp	4.20	3.86	3.53	CALL
ANM-1508	Type N Male	Low Loss 240-Series	Crimp	4.10	3.77	3.44	CALL
ANM-1516	Type N Male, Right Angle	Low Loss 240-Series	Crimp	7.35	6.76	6.17	CALL
ANM-1304	Type N Male	Low Loss 300-Series	Crimp	4.10	3.77	3.44	CALL
ANM-1416	Type N Male, Right Angle	Low Loss 400-Series	Crimp	4.94	4.54	4.15	CALL
ANM-1406	Type N Male	Low Loss 400-Series	Crimp	4.10	3.77	3.44	CALL
ANM-1420	Type N Male	Low Loss 400-Series	Solderless/Crimp	4.20	3.86	3.53	CALL
ANM-2400	Type N Male	Low Loss 400-Series	Clamp	4.36	4.01	3.66	CALL
ANM-2402	Type N Male, Right Angle	Low Loss 400-Series	Clamp	9.35	8.60	7.85	CALL
ANM-2602	Type N Male	Low Loss 600-Series	Clamp	6.20	5.70	5.21	CALL
ANM-1610	Type N Male	Low Loss 600-Series	Crimp	7.46	6.86	6.27	CALL
ANM-1616	Type N Male, Right Angle	Low Loss 600-Series	Crimp	7.35	6.76	6.17	CALL
ANM-2904	Type N Male	Low Loss 900-Series	Clamp	35.28	32.46	29.64	CALL
ANF-1A18	Type N Female	RG6	Crimp	4.20	3.86	3.53	CALL
BAC527	Type N Female	RG174/RG188/RG316	Crimp	8.51	8.00	7.49	CALL
BAC542	Type N Female, Bulkhead	RG55/RG141/RG142/RG223	Crimp	5.83	5.48	5.13	CALL
BAC544	Type N Female	RG55/RG141/RG142/RG223	Crimp	7.04	6.62	6.20	CALL
ANF-3700	Type N Female, Bulkhead	Low Loss 195-Series, RG58	Crimp	4.94	4.54	4.15	CALL
ANF-1700	Type N Female	Low Loss 195-Series, RG58	Crimp	4.10	3.77	3.44	CALL
ANF-5700	Type N Female, Panel Mount	Low Loss 195-Series, RG58	Crimp	4.36	4.01	3.66	CALL
ANF-1202	Type N Female	Low Loss 200-Series	Crimp	4.10	3.77	3.44	CALL
ANF-1508	Type N Female	Low Loss 240-Series	Crimp	4.10	3.77	3.44	CALL
ANF-1304	Type N Female	Low Loss 300-Series	Crimp	4.20	3.86	3.53	CALL
ANF-1406	Type N Female	Low Loss 400-Series	Crimp	4.10	3.77	3.44	CALL
ANF-2400	Type N Female	Low Loss 400-Series	Clamp	4.36	4.01	3.66	CALL
ANF-2602	Type N Female	Low Loss 600-Series	Clamp	5.88	5.41	4.94	CALL
ANF-1610	Type N Female	Low Loss 600-Series	Crimp	7.40	6.81	6.22	CALL
ANF-2906	Type N Female	Low Loss 900-Series	Clamp	35.28	32.46	29.64	CALL
ANF-2904	Type N Female, Times Microwave® #EZ-900-NFC-2	Low Loss 900-Series	Clamp	88.20	81.14	74.09	CALL
ARNJ-1700	Reverse Polarity Type N Jack	Low Loss 195-Series, RG58	Crimp	4.94	4.54	4.15	CALL
ARNJ-1404	Reverse Polarity Type N Jack	Low Loss 400-Series	Crimp	4.94	4.54	4.15	CALL
ARNP-1700	Reverse Polarity Type N Plug	Low Loss 195-Series, RG58	Crimp	4.94	4.54	4.15	CALL
ARNP-1404	Reverse Polarity Type N Plug	Low Loss 400-Series	Crimp	4.94	4.54	4.15	CALL

BNC Coaxial Connectors, 50 Ohm

BAC836A-58	BNC Male	RG58	Crimp	3.26	3.06	2.87	CALL
BAC836A-58P	BNC Male	RG58 Plenum	Crimp	4.10	3.85	3.61	CALL
BAC838-58	BNC Male	RG58	Twist On	4.99	4.69	4.39	CALL
BIF-83	BNC Male, Insulated	RG58	Crimp	5.04	4.74	4.44	CALL
BAC10A	BNC Male	RG58	Clamp	4.99	4.69	4.39	CALL
BAC547	BNC Male	RG142/RG223/RG400	Crimp	2.94	2.76	2.59	CALL
BAC836B-74	BNC Male	RG174/RG188/RG316	Crimp	5.57	5.24	4.90	CALL
BAC546	BNC Male, Right Angle	RG174/RG188/RG316	Crimp	5.57	5.24	4.90	CALL
ABM-1702	BNC Male, Right Angle	Low Loss 195-Series, RG58	Crimp	4.99	4.59	4.19	CALL
ABM-1704	BNC Male	Low Loss 195-Series, RG58	Solderless/Crimp	2.73	2.62	2.51	CALL
BAC515	BNC Female	RG58	Crimp	4.99	4.69	4.39	CALL
BAC522	BNC Female, Bulkhead	RG58	Crimp	6.20	5.83	5.46	CALL
BAC548	BNC Female	RG142	Crimp	5.46	5.13	4.80	CALL
BAC517	BNC Female	RG174/RG188/RG316	Crimp	4.99	4.69	4.39	CALL
BAC540	BNC Female	RG174/RG188/RG316	Crimp	5.88	5.53	5.17	CALL
ARBJ-1700	Reverse Polarity BNC Jack	Low Loss 195-Series, RG58	Crimp	3.68	3.39	3.09	CALL
ARBP-1700	Reverse Polarity BNC Plug	Low Loss 195-Series, RG58	Crimp	4.10	3.77	3.44	CALL
ARBP-1402	Reverse Polarity BNC Plug	Low Loss 400-Series	Crimp	4.73	4.35	3.97	CALL

BNC Coaxial Connectors, 75 Ohm

BAC026	BNC Male	RG6	Twist On	3.60	3.38	3.17	CALL
BAC032	BNC Male	RG6	Crimp (2 Pc)	3.55	3.34	3.12	CALL
BAC029	BNC Male	RG6	Crimp (3 Pc)	3.55	3.34	3.12	CALL
BAC042	BNC Male	RG6-Q	Crimp	2.45	2.30	2.16	CALL
BAC024	BNC Male	RG59	Twist On	3.60	3.38	3.17	CALL
BAC027	BNC Male	RG59 (23 AWG C.C.)	Crimp	3.55	3.34	3.12	CALL
BAC027A	BNC Male	RG59 (20 AWG C.C.)	Crimp	3.55	3.34	3.12	CALL
BAC028	BNC Male	RG59 Plenum	Crimp (3 Pc)	3.55	3.34	3.12	CALL
BAC030	BNC Male	RG59	Crimp (2 Pc)	3.55	3.34	3.12	CALL
BAC031	BNC Male	RG59 Plenum	Crimp (2 Pc)	3.55	3.34	3.12	CALL
BAC033	BNC Male	RG59	Solder	4.70	4.42	4.14	CALL
BAC543	BNC Male, Right Angle	RG59	Crimp	5.15	4.84	4.53	CALL
BAC706	BNC Male, Right Angle	RG59/6	Crimp	6.25	5.88	5.50	CALL
BAC985	BNC Male, Right Angle	RG59/6	Twist On	6.35	5.97	5.59	CALL
BAC836A-59	BNC Male	RG59/6	Crimp	3.00	2.82	2.64	CALL
BAC551	BNC Male, Right Angle	RG179/RG187	Crimp	5.70	5.36	5.02	CALL
BAC836B-87	BNC Male	RG187/CTL	Crimp	3.00	2.82	2.64	CALL
BAC516	BNC Female	RG6	Crimp	4.35	4.09	3.83	CALL
BAC014	BNC Female	RG59	Twist On	4.35	4.09	3.83	CALL
BAC908-59	BNC Female	RG59/6	Crimp	4.35	4.09	3.83	CALL
BAC552	BNC Female, Bulkhead	RG59	Crimp	5.80	5.45	5.10	CALL
BAC550	BNC Female, Bulkhead	RG179	Crimp	4.40	4.14	3.87	CALL

Some Connectors are sold in 10-Packs. See website for details. Adapters are sold individually.

