



Item #	Description	Color	1-9	10-24	25-99	100+
--------	-------------	-------	-----	-------	-------	------

**USB Revision 2.0 Compliant Bulk Cable**

This cable will support the 480 Mbps transmission rate of a USB 2.0 network and is also backward compatible with older, slower USB networks. USB bulk cable features two 20 AWG power conductors plus one 28 AWG twisted pair for the data lines.

CSUSB-100	USB Revision 2.0 Compliant Bulk Cable, 100ft (30.5m) Spool	Lt. Gray	56.79	53.38	49.98	CALL
CSUSB-500	USB Revision 2.0 Compliant Bulk Cable, 500ft (152.4m) Spool	Lt. Gray	260.49	244.86	229.23	CALL
CSUSB-1000	USB Revision 2.0 Compliant Bulk Cable, 1000ft (304.8m) Spool	Lt. Gray	457.26	429.82	402.39	CALL

**USB Revision 2.0 Compliant Bulk Cable**

USB bulk cable features two 24 or 28 AWG power conductors plus one 28 AWG twisted pair for the data lines.

CBL-USB2-2824-100	USB Revision 2.0 Compliant Bulk Cable, 100ft (30.5m) Spool	Black	40.94	38.48	36.03	CALL
CBL-USB2-2824-500	USB Revision 2.0 Compliant Bulk Cable, 500ft (152.4m) Spool	Black	187.41	176.17	164.92	CALL
CBL-USB2-2824-1000	USB Revision 2.0 Compliant Bulk Cable, 1000ft (304.8m) Spool	Black	335.04	314.94	294.84	CALL
CBL-USB2-2828-100	USB Revision 2.0 Compliant Bulk Cable, 100ft (30.5m) Spool	Black	28.44	26.73	25.03	CALL
CBL-USB2-2828-500	USB Revision 2.0 Compliant Bulk Cable, 500ft (152.4m) Spool	Black	122.73	115.37	108.00	CALL
CBL-USB2-2828-1000	USB Revision 2.0 Compliant Bulk Cable, 1000ft (304.8m) Spool	Black	221.43	208.14	194.86	CALL

**LSZH USB Revision 2.0 Compliant Bulk Cable**

Halogen free USB bulk cable features two 20 AWG power conductors plus one 28 AWG twisted pair for the data lines. A flexible LSZH jacket covers the braid, foil and drain wire shield.

CBL-USBZ-2820-100	LSZH USB Revision 2.0 Compliant Bulk Cable, 100ft (30.5m) Spool	Black	119.27	112.11	104.96	CALL
CBL-USBZ-2820-500	LSZH USB Revision 2.0 Compliant Bulk Cable, 500ft (152.4m) Spool	Black	562.16	528.43	494.70	CALL
CBL-USBZ-2820-1000	LSZH USB Revision 2.0 Compliant Bulk Cable, 1000ft (304.8m) Spool	Black	1022.06	960.74	899.41	CALL

**USB Connectors and Hoods, Type A and B**

USB connectors and hoods are now available for custom lengths and applications. Connectors feature gold plated solder contacts, nickel-plated steel shells and a UL94V-0 rated housing.

USBCN2.0-A	USB Type A Connector		1.63	1.60	1.53	CALL
USBCN2.0-B	USB Type B Connector		1.63	1.60	1.53	CALL
USBHD2.0-Z-A	LSZH USB Type A Hood	Black	1.05	1.03	0.99	CALL
USBHD2.0-Z-B	LSZH USB Type B Hood	Black	1.05	1.03	0.99	CALL
USBHD2.0-A	USB Type A Hood	Lt. Gray	0.74	0.73	0.70	CALL
USBHD2.0-B	USB Type B Hood	Lt. Gray	0.74	0.73	0.70	CALL

**USB Type A and B Female Field Termination Connector**

The USB field termination female connectors provide an easy and convenient way to perform field termination for USB applications. USB 2.0 standard A and B connector styles are available. Separate connection points are provided for all 4 positions of the connector plus the ground. Terminal block design with set screws provides reliable electrical connections utilizing no special tools. The terminal block area is clearly marked making proper termination virtually foolproof. Panel mountable using 4-40 screws provided.

USBAFT	USB Field Termination Connector, Type A Female		6.99	6.57	6.15	CALL
USBFT	USB Field Termination Connector, Type B Female		6.99	6.57	6.15	CALL

**USB Panel Mountable PCB Connectors - Type A and B**

This unique L-com design allows an easy, efficient way to mount USB 2.0 Type A and B PCB connectors using 4-40 screws. 30 microinch gold plated contacts insure many mating cycles without compromising performance. These are the same connectors used in our field termination terminal block connectors. PCB connectors sold in packages of 10.

UC-A-PMT	USB Panel Mount Type A PCB Connector	Silver	14.29	13.43	12.58	CALL
UC-B-PMT	USB Panel Mount Type B PCB Connector	Silver	14.29	13.43	12.58	CALL

**USB Type A, B, Mini B5 and Micro B Female Connector Covers - Protect Unused Ports, Pkg/10**

These covers are perfect for protecting unused female ports in our panel mount couplers or any expensive equipment from physical damage, dirt and dust. Made from soft ABS, these covers attach easily and stay in place with a snug friction fit.

CAPUSB-A	USB Protective Cover for Type A Jacks, Pkg/10	Black	7.51	6.91	6.31	CALL
CAPUSB-B	USB Protective Cover for Type B Jacks, Pkg/10	Black	7.51	6.91	6.31	CALL
CAPUSB-MB5	USB Protective Cover for Type Mini B5 Jacks, Pkg/10	Black	7.51	6.91	6.31	CALL
CAPUSB-MICB	USB Protective Cover for Type Micro B Jacks, Pkg/10	Black	7.51	6.91	6.31	CALL

**USB Cable Assembly Male Connector Dust Covers - Pkg/10**

These hard to find covers are perfect for protecting unused USB cable assembly connectors from physical damage, dirt and dust. Made from PVC, they attach easily and stay in place with a snug friction fit.

CVRUSB-A	USB Protective Cover for USB 2.0 and 3.0 Type A Plugs, Pkg/10	Black	6.35	5.84	5.33	CALL
CVRUSB-B	USB Protective Cover for USB 2.0 Type B Plugs, Pkg/10	Black	6.35	5.84	5.33	CALL
CVRUSB-MB4	USB Protective Cover for USB 2.0 Type Mini B4 Plugs, Pkg/10	Black	6.35	5.84	5.33	CALL
CVRUSB-MB5	USB Protective Cover for USB 2.0 Type Mini B5 Plugs, Pkg/10	Black	6.35	5.84	5.33	CALL
CVRUSB-MICB	USB Protective Cover for USB 2.0 Type Micro B Plugs, Pkg/10	Black	6.35	5.84	5.33	CALL
CVRUSB3.0-B	USB Protective Cover for USB 3.0 Type B Plugs, Pkg/10	Black	6.35	5.84	5.33	CALL
CVRUSB3.0-MICB	USB Protective Cover for USB 3.0 Type Micro B Plugs, Pkg/10	Black	6.35	5.84	5.33	CALL

**USB Protective Covers with Lanyard - for Type A and B Jacks - Pkg/10**

These new covers add a lanyard feature to enhance our existing USB cover product line. They are perfect for protecting unused USB female ports in our panel mount couplers or any expensive equipment from physical damage, dirt and dust. The lanyard is perfectly sized to fit the 4-40 screws used in our ECF and UPM panel mount products. Made from soft polyethylene, these covers attach easily and stay in place with a snug friction fit.

CAP-A-USB-LAN	USB Protective Cover with Lanyard for USB Type A Jacks, Pkg/10	Black	7.82	7.19	6.57	CALL
CAP-B-USB-LAN	USB Protective Cover with Lanyard for USB Type B Jacks, Pkg/10	Black	7.82	7.19	6.57	CALL

