

More lengths available.
Go to L-com.com



CAVISU3AB-2-M

CAVISU3AMICB-2-M

Best Seller

CSMUAB-M

Best Seller

ECUSBAA-M

ECUSBAX

CSMUCLRAA-M

CSMUCLRAB-M

CAUBLKAB-M

Item #	Description	Color	1-9	10-24	25-99	100+
USB 3.0 Cables - Type A and B with Thumbscrews						
CAVISU3AB-2-03M	USB 3.0 Cable, Type A/Type B with Thumbscrews, 0.3m	Blue	17.10	16.07	15.05	CALL
CAVISU3AB-2-05M	USB 3.0 Cable, Type A/Type B with Thumbscrews, 0.5m	Blue	17.50	16.45	15.40	CALL
CAVISU3AB-2-1M	USB 3.0 Cable, Type A/Type B with Thumbscrews, 1.0m	Blue	18.50	17.39	16.28	CALL
CAVISU3AB-2-2M	USB 3.0 Cable, Type A/Type B with Thumbscrews, 2.0m	Blue	20.50	19.27	18.04	CALL
CAVISU3AB-2-3M	USB 3.0 Cable, Type A/Type B with Thumbscrews, 3.0m	Blue	22.50	21.15	19.80	CALL
CAVISU3AB-2-5M	USB 3.0 Cable, Type A/Type B with Thumbscrews, 5.0m	Blue	26.50	24.91	23.32	CALL
USB 3.0 Cables - Type A and Micro B with Thumbscrews						
CAVISU3AMICB-2-03M	USB 3.0 Cable, Type A/Type Micro B with Thumbscrews, 0.3m	Blue	17.10	16.07	15.05	CALL
CAVISU3AMICB-2-05M	USB 3.0 Cable, Type A/Type Micro B with Thumbscrews, 0.5m	Blue	17.50	16.45	15.40	CALL
CAVISU3AMICB-2-1M	USB 3.0 Cable, Type A/Type Micro B with Thumbscrews, 1.0m	Blue	18.50	17.39	16.28	CALL
CAVISU3AMICB-2-2M	USB 3.0 Cable, Type A/Type Micro B with Thumbscrews, 2.0m	Blue	20.50	19.27	18.04	CALL
CAVISU3AMICB-2-3M	USB 3.0 Cable, Type A/Type Micro B with Thumbscrews, 3.0m	Blue	22.50	21.15	19.80	CALL
CAVISU3AMICB-2-5M	USB 3.0 Cable, Type A/Type Micro B with Thumbscrews, 5.0m	Blue	26.50	24.91	23.32	CALL
Premium USB 2.0 Cables - Type A to Type A Con., PVC Jacket, 30μ (0.762μm) Gold, 20 AWG Power Leads						
Premium USB 2.0 cables contain 20 AWG power wires for maximum power transfer.						
CSMUAA-03M	Premium USB Cable, Type A/A, 0.3m	Lt. Gray	7.75	7.13	6.51	CALL
CSMUAA-05M	Premium USB Cable, Type A/A, 0.5m	Lt. Gray	7.95	7.31	6.68	CALL
CSMUAA-1M	Premium USB Cable, Type A/A, 1.0m	Lt. Gray	8.45	7.77	7.10	CALL
CSMUAA-2M	Premium USB Cable, Type A/A, 2.0m	Lt. Gray	9.45	8.69	7.94	CALL
CSMUAA-4M	Premium USB Cable, Type A/A, 4.0m	Lt. Gray	11.95	10.99	10.04	CALL
CSMUAA-5M	Premium USB Cable, Type A/A, 5.0m	Lt. Gray	12.45	11.45	10.46	CALL
Premium USB 2.0 Cables - Type A to Type B Con., PVC Jacket, 30μ (0.762μm) Gold, 20 AWG Power Leads						
CSMUAB-03M	Premium USB Cable, Type A/B, 0.3m	Lt. Gray	6.75	6.21	5.67	CALL
CSMUAB-075M	Premium USB Cable, Type A/B, 0.75m	Lt. Gray	7.20	6.62	6.05	CALL
CSMUAB-1M	Premium USB Cable, Type A/B, 1.0m	Lt. Gray	7.45	6.85	6.26	CALL
CSMUAB-2M	Premium USB Cable, Type A/B, 2.0m	Lt. Gray	8.45	7.77	7.10	CALL
CSMUAB-3M	Premium USB Cable, Type A/B, 3.0m	Lt. Gray	9.45	8.69	7.94	CALL
CSMUAB-4M	Premium USB Cable, Type A/B, 4.0m	Lt. Gray	10.45	9.61	8.78	CALL
CSMUAB-5M	Premium USB Cable, Type A/B, 5.0m	Lt. Gray	11.45	10.53	9.62	CALL
Premium USB 2.0 Ext. Cables - Type A Male to Female, PVC Jacket, 30μ (0.762μm) Gold, 20 AWG Power Leads						
CSMUAX-05M	Premium USB Extension Cable, Type A Male/Female, 0.5m	Lt. Gray	7.45	7.15	6.85	CALL
CSMUAX-1M	Premium USB Extension Cable, Type A Male/Female, 1.0m	Lt. Gray	7.95	7.63	7.31	CALL
CSMUAX-2M	Premium USB Extension Cable, Type A Male/Female, 2.0m	Lt. Gray	8.95	8.59	8.23	CALL
CSMUAX-3M	Premium USB Extension Cable, Type A Male/Female, 3.0m	Lt. Gray	9.95	9.55	9.15	CALL
Deluxe USB 2.0 Cables - Type A to A or A to B Connectors, 30μ (0.762μm) Gold, 26 AWG Power Leads						
L-com's standard USB cable offering, the ECUSB series, provides high performance at competitive prices. These quality constructed cables feature USB 2.0 Compliant 26 AWG power leads and are finished in an attractive medium gray color.						
ECUSBAA-05M	Deluxe USB Cable, Type A/A, 0.5m	Gray	4.85	4.37	3.88	CALL
ECUSBAA-1M	Deluxe USB Cable, Type A/A, 1.0m	Gray	5.25	4.73	4.20	CALL
ECUSBAA-2M	Deluxe USB Cable, Type A/A, 2.0m	Gray	6.05	5.45	4.84	CALL
ECUSBAA-3M	Deluxe USB Cable, Type A/A, 3.0m	Gray	6.85	6.17	5.48	CALL
ECUSBAA-4M	Deluxe USB Cable, Type A/A, 4.0m	Gray	7.65	6.89	6.12	CALL
ECUSBAA-5M	Deluxe USB Cable, Type A/A, 5.0m	Gray	8.45	7.60	6.76	CALL
ECUSBAB-05M	Deluxe USB Cable, Type A/B, 0.5m	Gray	4.35	3.91	3.48	CALL
ECUSBAB-075M	Deluxe USB Cable, Type A/B, 0.75m	Gray	4.55	4.09	3.64	CALL
ECUSBAB-1M	Deluxe USB Cable, Type A/B, 1.0m	Gray	4.75	4.28	3.80	CALL
ECUSBAB-2M	Deluxe USB Cable, Type A/B, 2.0m	Gray	5.55	5.00	4.44	CALL
ECUSBAB-3M	Deluxe USB Cable, Type A/B, 3.0m	Gray	6.35	5.71	5.08	CALL
ECUSBAB-5M	Deluxe USB Cable, Type A/B, 5.0m	Gray	7.95	7.16	6.36	CALL
Deluxe USB Extension Cables - Type A Male to Female, 30 Microinches (0.762μm) Gold, 26 AWG Power Leads						
ECUSBAX-03M	Deluxe USB Extension Cable, Type A Male/Female, 0.3m	Gray	4.70	4.51	4.32	CALL
ECUSBAX-05M	Deluxe USB Extension Cable, Type A Male/Female, 0.5m	Gray	4.85	4.66	4.46	CALL
ECUSBAX-075M	Deluxe USB Extension Cable, Type A Male/Female, 0.75m	Gray	5.05	4.85	4.65	CALL
ECUSBAX-1M	Deluxe USB Extension Cable, Type A Male/Female, 1.0m	Gray	5.25	5.04	4.83	CALL
ECUSBAX-2M	Deluxe USB Extension Cable, Type A Male/Female, 2.0m	Gray	6.05	5.81	5.57	CALL
ECUSBAX-3M	Deluxe USB Extension Cable, Type A Male/Female, 3.0m	Gray	6.85	6.58	6.30	CALL
Premium USB 2.0 Cables - Type A to A or A to B Connectors, Clear Jacket and Mold						
These sharp looking cables highlight L-com's high quality standards when "looking under the hood". A metal shielding can under the mold and high coverage braid shield protect your data even in the noisiest electrical environments. These cables use the same design as the popular CSMUAB series featuring 20 AWG power conductors enabling maximum power transfer from host to peripheral.						
CSMUCLRAA-03M	Premium USB Cable, Type A/A, 0.3m	Clear	7.85	7.22	6.59	CALL
CSMUCLRAA-05M	Premium USB Cable, Type A/A, 0.5m	Clear	8.05	7.41	6.76	CALL
CSMUCLRAA-1M	Premium USB Cable, Type A/A, 1.0m	Clear	8.65	7.96	7.27	CALL
CSMUCLRAA-2M	Premium USB Cable, Type A/A, 2.0m	Clear	9.85	9.06	8.27	CALL
CSMUCLRAA-3M	Premium USB Cable, Type A/A, 3.0m	Clear	11.05	10.17	9.28	CALL
CSMUCLRAA-5M	Premium USB Cable, Type A/A, 5.0m	Clear	13.45	12.37	11.30	CALL
CSMUCLRAB-03M	Premium USB Cable, Type A/B, 0.3m	Clear	6.85	6.30	5.75	CALL
CSMUCLRAB-05M	Premium USB Cable, Type A/B, 0.5m	Clear	7.05	6.49	5.92	CALL
CSMUCLRAB-1M	Premium USB Cable, Type A/B, 1.0m	Clear	7.65	7.04	6.43	CALL
CSMUCLRAB-2M	Premium USB Cable, Type A/B, 2.0m	Clear	8.85	8.14	7.43	CALL
CSMUCLRAB-3M	Premium USB Cable, Type A/B, 3.0m	Clear	10.05	9.25	8.44	CALL
CSMUCLRAB-5M	Premium USB Cable, Type A/B, 5.0m	Clear	12.45	11.45	10.46	CALL
Premium USB 2.0 Cables - Type A to A or A to B Connectors, Black, 30μ (0.762μm) Gold, 24 AWG Power Leads						
CAUBLKAA-03M	Premium USB Cable, Type A/A, 0.3m	Black	5.50	5.06	4.62	CALL
CAUBLKAA-05M	Premium USB Cable, Type A/A, 0.5m	Black	5.70	5.24	4.79	CALL
CAUBLKAA-1M	Premium USB Cable, Type A/A, 1.0m	Black	6.15	5.66	5.17	CALL
CAUBLKAA-3M	Premium USB Cable, Type A/A, 3.0m	Black	7.95	7.31	6.68	CALL
CAUBLKAA-5M	Premium USB Cable, Type A/A, 5.0m	Black	9.75	8.97	8.19	CALL
CAUBLKAB-03M	Premium USB Cable, Type A/B, 0.3m	Black	5.00	4.60	4.20	CALL
CAUBLKAB-05M	Premium USB Cable, Type A/B, 0.5m	Black	5.20	4.78	4.37	CALL
CAUBLKAB-1M	Premium USB Cable, Type A/B, 1.0m	Black	5.65	5.20	4.75	CALL
CAUBLKAB-3M	Premium USB Cable, Type A/B, 3.0m	Black	7.45	6.85	6.26	CALL
CAUBLKAB-5M	Premium USB Cable, Type A/B, 5.0m	Black	9.25	8.51	7.77	CALL