



Best Seller



Installation of Mini DIN bulkhead adapter styles



Mount adapter from the front of panel, secure threads / nut from the back of the panel.

Mount adapter from the rear of panel, secure threads / nut from the front of the panel.



Item #	Description	1-9	10-24	25-99	100+
--------	-------------	-----	-------	-------	------

Mini DIN Feed-thru Adapters - Panel and Wall Plate Mountable

These exclusive adapters offer a unique design suitable for panel mounting Mini DIN adapters. Female-Female gender.

MD44FF	Mini DIN 4 Feed-Thru Adapter, Female / Female	9.24	8.50	7.76	CALL
MD44FJF	Mini DIN 4 Bulkhead Jack / Leads, Front Mount	10.30	9.48	8.65	CALL
MD44FJR	Mini DIN 4 Bulkhead Jack / Leads, Rear Mount	10.30	9.48	8.65	CALL

Type F Within Series Adapters - 75 Ohm

BA122	Coaxial Adapter, Type F Male / Male	2.15	2.02	1.89	CALL
BA123	Coaxial Adapter, Type F Female / Male, Right Angle	2.15	2.02	1.89	CALL
BA124	Coaxial Adapter, Type F Male Push-on / Female	1.35	1.27	1.19	CALL
BA330A	Coaxial Bulkhead Adapter, Type F Female / Female, (5/1.3cm D-Hole), Insulated	2.15	2.02	1.89	CALL

RCA Female Feed-Thru Adapter - with Red, Green, Blue, Yellow or White Insulators

These RCA feed-thru adapters feature insulators color coded for both video and audio applications. This color coding assists in component hookup to avoid improper connections.

BA400R	Coaxial Adapter, RCA Bulkhead Female / Female, Red Insulator	3.95	3.71	3.48	CALL
BA400G	Coaxial Adapter, RCA Bulkhead Female / Female, Green Insulator	3.95	3.71	3.48	CALL
BA400B	Coaxial Adapter, RCA Bulkhead Female / Female, Blue Insulator	3.95	3.71	3.48	CALL
BA400Y	Coaxial Adapter, RCA Bulkhead Female / Female, Yellow Insulator	3.95	3.71	3.48	CALL
BA400W	Coaxial Adapter, RCA Bulkhead Female / Female, White Insulator	3.95	3.71	3.48	CALL
BA400A	Coaxial Adapter, RCA Bulkhead Female / Female, 0.5" (1.3cm) Circular Hole	3.95	3.71	3.48	CALL

RCA Interseries Coaxial Adapter / 75 Ohm

BA907	Coaxial Adapter, RCA Male / Type F Female	2.15	2.02	1.89	CALL
-------	---	------	------	------	------

3.5mm Audio Bulkhead Coupler

L-com's 3.5mm audio bulkhead coupler offers a practical and economical way to feed audio cables through panels, wall plates and enclosures. The .50" D-hole design and lock washer ensure a secure fit. This versatile coupler is also available pre-mounted on L-com's USP2-35MM and USP4-35MM two port and four port Universal Sub Panels.

BA35FF	3.5mm Audio Bulkhead Coupler	8.15	7.50	6.85	CALL
--------	------------------------------	------	------	------	------

Right Angle RCA and TS 1/4" Male / Female Adapters

L-com's low profile right angle audio adapters are perfect for tight fit applications. Two options are available, RCA and TS 1/4", allowing cables and connectors to fit in small spaces. These adapters are male to female and can be attached at any angle to allow for any 360 degree option. Durable molded design can take punishment in the field and gold plated contacts provide optimum performance.

RA-RCAMF	RCA Right Angle Adapter, Male / Female	3.85	3.54	3.23	CALL
RA-14M214F	TS 1/4" Right Angle Adapter, Male / Female	5.45	5.01	4.58	CALL

Adapters and Gender Changers

It's often necessary to connect between different interface types or to change the gender of an interface to allow attachment of extension cables. We offer a wide variety of adapters and gender changers covering commonly used interfaces such as HD15, Mini DIN 5 and 6, DB9, DVI and HDMI.

HD15 Slimline Gender Changer / Adapters - Fully Populated

DGBH15F	Slimline Gender Changer, HD15 Female / Female	7.95	7.16	6.36	CALL
DGBH15M	Slimline Gender Changer, HD15 Male / Male	7.95	7.16	6.36	CALL
DGBH15MF	Slimline Socket Saver, HD15 Male / Female	7.95	7.16	6.36	CALL

Slimline Gender Changer / Adapters - with Pin 9 Missing to Interface VGA Monitors

DGBV15F	Slimline Gender Changer, HD15 Female / Female, No Pin 9	8.35	7.51	6.68	CALL
DGBV15M	Slimline Gender Changer, HD15 Male / Male, No Pin 9	8.35	7.51	6.68	CALL
DGBV15MF	Slimline Socket Saver, HD15 Male / Female, No Pin 9	8.35	7.51	6.68	CALL

HD15 Low Profile Right Angle Adapters - Molded and Fully Shielded

Connecting cables in tight spaces can be a problem in many applications. These low profile adapters solve this problem by allowing cables to be connected at a 90 degree angle. Two versions are available to allow cables to exit in opposite directions. Adapters are male to female, fully shielded and are overmolded with Gray PVC. Mating hardware is reversible allowing for use in virtually any application.

DG90H15MF1	Low Profile Right Angle Adapter, HD15 Male / Female, Cable Exit 1	8.91	8.38	7.84	CALL
DG90H15MF2	Low Profile Right Angle Adapter, HD15 Male / Female, Cable Exit 2	8.91	8.38	7.84	CALL

DVI Dust Covers - Male and Female

L-com's DVI dust covers protect unused DVI connectors on cable assemblies and DVI receptacles on DVI equipment including DVI KVM switches, DVI Extenders, DVI splitters, and more. We offer both male and female DVI dust covers in packages of 10.

CVRDVI-M	DVI Dust Cover, Male, Pkg / 10	6.15	5.90	5.66	CALL
CVRDVI-F	DVI Dust Cover, Female, Pkg / 10	6.15	5.90	5.66	CALL

HDMI® Dust Covers - Male and Female

L-com's HDMI dust covers protect unused HDMI connectors on cable assemblies and HDMI receptacles on HDMI equipment including HDMI hubs, HDMI Extenders, HDMI splitters, and more. We offer both male and female HDMI dust covers in packages of 10.

CVRHD-M	HDMI Dust Cover, Male, Pkg / 10	6.15	5.90	5.66	CALL
CVRHD-F	HDMI Dust Cover, Female, Pkg / 10	6.15	5.90	5.66	CALL