


**Bulk Fiber Optic Cabling - Sold by the Meter (1m = 3.28ft)**

L-com offers the most popular types of Simplex, Duplex, Breakout and Distribution style cables. All are available from stock in 1 meter intervals with a 25 meter minimum unless otherwise noted. Other cabling types are available by request. Jacket color of bulk cable may vary. Contact L-com today for custom termination of bulk cable. **NOTE:** Bulk cable custom lengths are non-returnable.

*How do fiber optics work?*



[L-com.com/videos/A15](http://L-com.com/videos/A15)



| Item # | Description | Color | 1-9 |
|--------|-------------|-------|-----|
|--------|-------------|-------|-----|

**9/125 Single mode Bulk Fiber Cable**

**DISTRIBUTION STYLE WITH 900µm SUB UNITS**

|             |  |        |       |
|-------------|--|--------|-------|
| FOBSNGD6-M  | Single mode 6 Count Indoor/Outdoor OFNP Bulk Fiber Distribution Cable  | Yellow | 2.60  |
| FOBSNGD12-M | Single mode 12 Count Indoor/Outdoor OFNP Bulk Fiber Distribution Cable | Yellow | 7.20  |
| FOBSNGD24-M | Single mode 24 Count Indoor/Outdoor OFNP Bulk Fiber Distribution Cable | Yellow | 11.60 |

**BREAKOUT STYLE WITH 2mm SUB UNITS**

|             |  |        |       |
|-------------|--|--------|-------|
| FOB0S1B2-M  | Single mode 2 Count Indoor/Outdoor OFNP Bulk Fiber Breakout Cable  | Yellow | 5.10  |
| FOB0S1B4-M  | Single mode 4 Count Indoor/Outdoor OFNP Bulk Fiber Breakout Cable  | Yellow | 5.75  |
| FOB0S1B6-M  | Single mode 6 Count Indoor/Outdoor OFNP Bulk Fiber Breakout Cable  | Yellow | 7.90  |
| FOB0S1B12-M | Single mode 12 Count Indoor/Outdoor OFNP Bulk Fiber Breakout Cable | Yellow | 12.70 |

**PATCH STYLE SIMPLEX OR DUPLEX (ZIPCORD) WITH 2mm CABLE OD**

|           |   |        |      |
|-----------|---|--------|------|
| FOB0S1S-M | Single mode Simplex Indoor OFNR Bulk Fiber Cable          | Yellow | 1.15 |
| FOB0S1Z-M | Single mode Duplex (Zipcord) Indoor OFNR Bulk Fiber Cable | Yellow | 1.80 |

| Item # | Description | Body | Sleeve | 1-9 |
|--------|-------------|------|--------|-----|
|--------|-------------|------|--------|-----|

**Fiber Optic Single mode Couplers/Adapters - Multimode Options on pages 205, 212 and 213**

Need to join two single mode cables with the same connector types? Use these fiber optic couplers which utilize precise ceramic sleeves best suited to single mode applications.

**LC, SC and ST STYLES (see L-com.com for additional styles and options)**

|           |  |         |         |       |
|-----------|--|---------|---------|-------|
| FOA-500A  | Simplex LC / LC Coupler Low Profile          | Plastic | Ceramic | 10.25 |
| FOA-550A  | Duplex LC / LC Coupler Low Profile           | Plastic | Ceramic | 14.20 |
| FOA-801   | Duplex LC / LC Coupler with Mounting Flange  | Plastic | Ceramic | 13.35 |
| FOA-570   | Quad LC / LC Coupler with Mounting Flange    | Plastic | Ceramic | 20.55 |
| FOA-002A  | Simplex SC / SC Coupler with Mounting Flange | Plastic | Ceramic | 5.70  |
| FOA-002MA | Simplex SC / SC Coupler with Mounting Flange | Metal   | Ceramic | 8.05  |
| FOA-005A  | Duplex SC / SC Coupler with Mounting Flange  | Plastic | Ceramic | 8.25  |
| FOA-005MA | Duplex SC / SC Coupler with Mounting Flange  | Metal   | Ceramic | 10.50 |
| FOA-001A  | Simplex ST / ST Coupler with D Hole Mount    | Metal   | Ceramic | 5.15  |
| FOA-011A  | Simplex ST / ST Coupler with Mounting Flange | Metal   | Ceramic | 5.15  |
| FOA-401A  | Duplex ST / ST Coupler with Mounting Flange  | Metal   | Ceramic | 10.30 |

Need to change from one type of single mode connector to another? Use these fiber optic adapters.

**LC, SC and ST STYLES (see L-com.com for additional styles and options)**

|           |  |         |         |       |
|-----------|--|---------|---------|-------|
| FOA-014   | Simplex LC / SC Adapter Low Profile            | Plastic | Ceramic | 46.20 |
| FOA-020C  | Simplex LC / SC Adapter with Mounting Flange   | Plastic | Ceramic | 32.00 |
| FOA-006   | Duplex SC / ST Adapter with Mounting Flange    | Plastic | Ceramic | 10.85 |
| FOA-006MA | Duplex ST / SC Adapter with Mounting Flange    | Metal   | Ceramic | 14.95 |
| FOA-211A  | Simplex SC / ST Adapter with Rectangular Mount | Metal   | Ceramic | 10.00 |

| Item # | Description | 1-9 |
|--------|-------------|-----|
|--------|-------------|-----|

**9/125 Single mode Fiber Optic Pigtailed - 900µm, 2mm or 3mm OFNR Jackets**

L-com's fiber optic pigtailed provide a fast way to make factory terminations in the field. They can easily be fusion or mechanically spliced to an existing fiber line. All connectors utilize PC polish and all jackets are Riser (OFNR) rated. See [L-com.com](http://L-com.com) for complete listings including additional connectors, modes and 900µm 12 packs which contain one cable of every standard fiber color (such as FPT9SNG-LC-12PK) so you don't have to purchase the different colors individually.

**PIGTAIL CABLES - 900µm**




|                 |   |      |
|-----------------|---|------|
| FPT9SNG-LC-__-1 | Single mode Fiber Optic Pigtail, OFNR Jacket, 900µm, 1.0m | 4.45 |
| FPT9SNG-LC-__-2 | Single mode Fiber Optic Pigtail, OFNR Jacket, 900µm, 2.0m | 4.80 |
| FPT9SNG-LC-__-3 | Single mode Fiber Optic Pigtail, OFNR Jacket, 900µm, 3.0m | 5.15 |

**PIGTAIL CABLES - 2mm (Only available in: BLU, BRN, GRN, ORG, RED, WHT or YLW)**

|                 |   |      |
|-----------------|---|------|
| FPT2SNG-LC-__-1 | Single mode Fiber Optic Pigtail, OFNR Jacket, 2mm, 1.0m | 4.45 |
| FPT2SNG-LC-__-2 | Single mode Fiber Optic Pigtail, OFNR Jacket, 2mm, 2.0m | 4.80 |
| FPT2SNG-LC-__-3 | Single mode Fiber Optic Pigtail, OFNR Jacket, 2mm, 3.0m | 5.15 |

**PIGTAIL CABLES - 3mm (Only available in: BLU, GRN, ORG, RED or YLW)**

|                 |   |      |
|-----------------|---|------|
| FPT3SNG-LC-__-1 | Single mode Fiber Optic Pigtail, OFNR Jacket, 3mm, 1.0m | 4.45 |
| FPT3SNG-LC-__-2 | Single mode Fiber Optic Pigtail, OFNR Jacket, 3mm, 2.0m | 4.80 |
| FPT3SNG-LC-__-3 | Single mode Fiber Optic Pigtail, OFNR Jacket, 3mm, 3.0m | 5.15 |



**Explanation of FPT Series Part Numbers**

**FPT9SNG- - -1**

- Series:** FPT9SNG
- Cable Size:** 9=900µm, 2=2mm, 3=3mm
- Mode:** SNG=9/125, OM1=62.5/125, OM2=50/125, OM3=50/125 10G
- Length:** 1=1.0m, 2=2.0m, 3=3.0m
- Cable Color:** BLK, GRY, YLW, ORG, BLU, GRN, RED, VIO, BRN, AQU, ROS, WHT
- Connector Style:** LC, ST, FC, SC

Complete Listings on [L-com.com](http://L-com.com)