



Item #	Description	1-9	10-24	25-99	100+
D-Sub Metal Hood Kits - Choice of Five Grommets to Satisfy all Size Requirements					
Cast alloy metal construction with a matte nickel plate finish over tin and copper for the best conductivity. Kit includes a set of five grommets and 4-40 thread mounting screws.					
SDC9AG	Assembled Hood Kit, DB9 Metal	2.82	2.65	2.48	CALL
SDC15AG	Assembled Hood Kit, DB15 Metal	4.08	3.84	3.59	CALL
SDC25AG	Assembled Hood Kit, DB25 Metal	4.29	4.03	3.78	CALL
SDC37AG	Assembled Hood Kit, DB37 Metal	5.66	5.32	4.98	CALL
SDC50AG	Assembled Hood Kit, DB50 Metal	5.97	5.61	5.25	CALL

4-40 Thumbscrews for SDC Metal and Plastic D-Sub Hood Kits					
Nickel plated steel, knurled, slotted thumbscrews are now available for the entire SDC family of D-Sub hoods.					
04X44S	SDC Thumbscrew, 4-40 Thread	0.48	0.44	0.40	CALL

Right Angle D-Sub Metal Hood Kits - Low Profile with Thumbscrews					
Right angle hoods offered for applications requiring a 90 degree cable exit. Cast alloy metal construction with a nickel plated finish.					
SDRA9AG	Right Angle Assembled Hood Kit, DB9 Metal	4.61	4.33	4.06	CALL
SDRA15AG	Right Angle Assembled Hood Kit, DB15 Metal	4.82	4.53	4.24	CALL
SDRA25AG	Right Angle Assembled Hood Kit, DB25 Metal	5.13	4.82	4.51	CALL

Replacement Grommets for SDC and SDR Metal Backshells					
These grommets are the same as supplied with the SDC and SDR metal backshell kits. Five different sizes are offered per backshell size to best fit cable diameter used.					
GROM-9&15	Replacement Grommets, SDC & SDR 9/15 Metal Backshells	0.79	0.73	0.66	CALL
GROM-25	Replacement Grommets, SDC & SDR 25 Metal Backshells	0.79	0.73	0.66	CALL
GROM-37&50	Replacement Grommets, SDC 37/50 Metal Backshells	0.95	0.87	0.80	CALL

4-40 Hex Jack Screws - Difficult to Find Hardware for Mounting D-Sub Connectors					
SDG250	Jack Screw Kit, .25 inch (0.6cm) Thread, .232 inch (0.6cm) Screwlock, Pkg/50	14.45	13.58	12.72	CALL
SDG300	Jack Screw Kit, .30 inch (0.8cm) Thread, .232 inch (0.6cm) Screwlock, Pkg/50	14.45	13.58	12.72	CALL
SDG400	Jack Screw Kit, .40 inch (1.0cm) Thread, .232 inch (0.6cm) Screwlock, Pkg/50	14.45	13.58	12.72	CALL
SDG400S	Jack Screw Kit, .40 inch (1.0cm) Thread, .197 inch (0.5cm) Screwlock, Pkg/50	14.45	13.58	12.72	CALL
SDG400XS	Jack Screw Kit, .40 inch (1.0cm) Thread, .160 inch (0.4cm) Screwlock, Pkg/50	14.88	13.99	13.09	CALL
SDG450XS	Jack Screw Kit, .45 inch (1.1cm) Thread, .160 inch (0.4cm) Screwlock, Pkg/50	14.88	13.99	13.09	CALL
SDG500	Jack Screw Kit, .50 inch (1.3cm) Thread, .232 inch (0.6cm) Screwlock, Pkg/50	14.45	13.58	12.72	CALL

Hex Standoff 4-40 Thread - Needed with Hood Kits to Convert Male to Female					
SDH	Hex Standoffs, .232 inch (0.6cm) Hex, Pkg/50	10.15	9.54	8.93	CALL
SDHS	Hex Standoffs, .195 inch (0.5cm) Hex, Pkg/50	10.15	9.54	8.93	CALL
SDH-160	Hex Standoffs, .160 inch (0.4cm) Hex, Pkg/50	9.85	9.26	8.67	CALL

4-40 Screw and Retainer Pair - For Use on Male D-Sub Connectors with Metal Tabs					
PDF1	Screws and Retainers, Chromate, Pkg/50	13.80	12.97	12.14	CALL

4-40 Screw and Guard - Replacement for Cable Connector Hoods Such as SDC Series					
SDK	Screws and Guards, Nickel Plate, Pkg/50	6.30	5.80	5.29	CALL

Stainless Wall Plates - Accept a Variety of D-Sub Connectors					
Wall plates that accept common D-Sub connectors are found to be useful by many installers.					
WPD109	Stainless Wall Plate, One DB9/HD15 Opening	3.09	2.90	2.72	CALL
WPD115	Stainless Wall Plate, One DB15/HD26 Opening	3.09	2.90	2.72	CALL
WPD125	Stainless Wall Plate, One DB25/HD44 Opening	3.09	2.90	2.72	CALL

Rotary Cable Strippers - Cut Cable Jackets					
These tools offer an economical and consistent cable jacket strip every time. Featuring easy to adjust cutting depth, these tools strip both around the cable perimeter and lengthwise. HT-325 strips cable jackets ranging from 0.125" (0.3cm) to 1.0" (2.5cm). MK02 strips cable jackets ranging from 0.18" (0.5cm) to 1.12" (2.8cm). Choose HT-325 for light duty use and MK02 for heavier duty use.					
MK02	Round Cable Stripper	36.19	35.47	34.74	CALL
HT-325	Economy Round Cable Jacket Stripper	16.05	15.73	15.41	CALL

Cable Ties and Cable Mounts					
Cable ties come in handy to secure cable assemblies in different applications. Four different sizes, in packages of 100 pieces each. Color is black. Cable tie mounts allow the user to secure wire and/or cable quickly and easily to a surface. Mounts can be secured with screws or adhesive. Material is UL94V-2 rated nylon, color is black.					
CTB-05	6 inch (20.3cm) Cable Ties, Pkg/100	8.00	7.52	7.04	CALL
CTB-07	8 inch (15.2cm) Cable Ties, Pkg/100	9.15	8.60	8.05	CALL
CTB-09	8.5 inch (21.6cm) Cable Ties, Pkg/100	10.30	9.68	9.06	CALL
CTB-12	11.5 inch (29.2cm) Cable Ties, Pkg/100	11.45	10.76	10.08	CALL
CTM-0.75	Black Cable Tie Mount, 0.75" (1.9cm), Pkg/10	4.35	4.00	3.65	CALL
CTM-1.5	Black Cable Tie Mount, 1.50" (3.8cm), Pkg/10	8.35	7.68	7.01	CALL

Expandable Sleeving - Pkg/100ft (30.5m), Polyester Material with VW-1 Flammability Rating					
Polyester expandable flexible tubing is ideal for protecting wire and/or cable. The open weave design allows for flexible routing, high resistance to abrasion and broad range of expansion. Available in .125" (0.3cm), .25" (0.6cm) and .5" (1.3cm) diameters, color is black with white tracer.					
TUBEXP-0.125	Expandable Braid Sleeving, .125" (0.3cm) Diameter, 100ft (30.5m)	22.45	20.65	18.86	CALL
TUBEXP-0.25	Expandable Braid Sleeving, .25" (0.6cm) Diameter, 100ft (30.5m)	28.20	25.94	23.69	CALL
TUBEXP-0.5	Expandable Braid Sleeving, .5" (1.3cm) Diameter, 100ft (30.5m)	38.55	35.47	32.38	CALL

Item #	Description	List Price			
3M Heat Shrink Tubing Kits					
3M's popular kits are versatile assortments of flexible polyolefin heat shrink tubing used in a variety of electronic and electrical applications. Each kit is packaged in a plastic box.					
SPVFP301-BLK	Heat Shrink Kit, Black Colors	66.99			
SPVFP301-ASST	Heat Shrink Kit, Assorted Colors	66.99			

3M Copper Foil Shielding Tape with Conductive Adhesive					
TAP1181-3/8	Copper Foil Shielding Tape, 2.6 MIL x 3/8 inch (1.0cm) W x 18 Yards (16.5m)	17.99			
TAP1181-3/4	Copper Foil Shielding Tape, 2.6 MIL x 3/4 inch (1.9cm) W x 18 Yards (16.5m)	35.29			