

1460 Kraffform Micro ESD pre-set torque screwdrivers (0.02-0.11 Nm) with quick-release chuck









Application: Suitable for bits with 4 mm Halfmoon drive (and Wera Serie 9) and 4 mm HIOS drive (and Wera Serie 21)

Design: With quick-release chuck for rapid bit change

Pre-set torque: 0,035 Nm, 0,05 Nm

Accuracy: ± 10%

Handle: Kraffform Micro with non-roll feature and rotating cap, multi-component

						
Code	Art.No.	Nm	Nm	mm		
05074800001 ¹⁾	1460 ESD	0.035	0,02-0,06	131	5 1/4"	1
05074810001 ¹⁾	1461 ESD	0.050	0.05-0.11	131	5 1/4"	1

¹⁾ Other pre-set values within the adjustable range can be delivered on request