



# Product Data Sheet

## Waterproof Digital Test Thermometer

Waterproof test thermometer with Max/Min and data hold function and stainless steel probe. Supplied complete with pocket case. Particularly suitable for use in dishwasher.



### Product Features

- Dishwasher safe to 88°C (190°F)
- Instant Reading
- Hold function
- Max/Min memory
- Slide-on pen clip which can be used as extendable handle
- IPX7
- Calibration feature
- °C/F selectable
- Wide measuring range

### Product Specifications

<b>Temperature Range:</b>	-40 to +250°C (-40 to 482°F)
<b>Resolution:</b>	0.1°C/0.1°F
<b>Sample Rate:</b>	5-6 seconds
<b>Accuracy:</b>	+/-1°C between -10 and 100°C
<b>IP Rating:</b>	IP X7
<b>Auto Shut Off:</b>	After 15-20 minutes of non use
<b>LCD Size:</b>	15mm x 25mm
<b>Probe Size:</b>	115mm x 4mm Ø
<b>Probe Tip:</b>	2.5mm
<b>Minimum Immersion:</b>	6mm
<b>Battery:</b>	1 x LR44
<b>CE:</b>	Approved
<b>ROHS/WEEE:</b>	Compliant
<b>Hazard Information (SDS):</b>	See <a href="http://www.brannan.co.uk">www.brannan.co.uk</a> for information
<b>Product Dimensions:</b>	Packaged - 270mm x 95mm x 20mm Unpackaged - 207mm x 35mm x 15mm
<b>Product Weight:</b>	Packaged - 76g Unpackaged - 42g (including battery)
<b>Display Card Weight:</b>	22g
<b>Display Card Dimensions:</b>	269mm x 94mm
<b>Display PVC Blister Weight:</b>	11g
<b>Display PVC Blister Dimensions:</b>	270mm x 95mm x 20mm



Description	Barcode	Product No
Waterproof Probe Thermometer	5 011405 311641	31/164/0

Please note: all information on this data sheet is correct at the time of printing, but our policy is one of continuous product development. We reserve the right to change specification without notice.

PDS 0242:14:R0

### Brannan Thermometers & Instrumentation

Leconfield Industrial Estate • Cleator Moor • Cumbria • CA25 5QE • UK

tel: +44 (0)1946 816600 fax: +44 (0)1946 816625 email: [sales@brannan.co.uk](mailto:sales@brannan.co.uk) web: [www.brannan.co.uk](http://www.brannan.co.uk)

