

European Region

BRIGHT



- Cree® XRE LED delivers 463 lumens in high mode, 369 lumens in medium and 125 lumens in low mode



CONVENIENT

- Light slides easily onto battery and secures with one easy to use knob
- Push button switch on handle



POWERFUL

- Casts useable light on objects up to 505 metres away in high mode



ECONOMICAL

- Light for 34 hours between battery changes in high mode
- 127-hour battery life in low mode
- Lifetime LED never needs replacing

638487

European Region



BENEFITS

- Survives a 1-metre drop test
- Strong spot with halo flood
- Swivel head to direct light
- Suited for search & rescue and security applications
- Three light levels – High for maximum brightness, Medium for maximum beam distance and Low for maximum battery life

Before Using Your Flashlight:

Please read all instructions and cautionary markings on the package and light


Product Detail:

- Designation:** Energizer Expert LED
SAP: 638487
Colour: Black
Power Source: LR820 6V Alkaline Lantern Battery
IEC: 4LR25-2
Lamp: One Cree® XRE White LED
Lamp Life (hr): Lifetime
- | Mode: | High | Medium | Low |
|----------------------------------|--------|--------|-----|
| Light Output (lumens): | 463 | 369 | 125 |
| Run Time (h:min): | 34 | 49 | 127 |
| Beam Distance (m): | 505 | 513 | 17 |
| Peak Beam Intensity (cd): | 64,000 | 66,000 | 72 |
- Typical Weight (g):** 7,930 with battery
893 without battery
Dimensions (mm): 204 x 232 x 92

Performance:

Run Time

Continuous Drain to End of Useable Light (21° C)



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a claim or warranty
 ©Energizer / All Rights Reserved