



20-60VA Electronic Transformer

For low voltage halogen lighting



SPECIFICATION

Input Voltage:	240V 50Hz
Output Voltage:	11.6V
VA:	20-60VA
Average Life:	30,000 - 35,000 hours
Guarantee:	8 years
Dimmable:	Yes
Protection:	Surge Protection Overload Protection Short Circuit Protection
Leads:	Pre-wired 2 x 11.6V (230mm) Pre-wired 1 x 220-240V (230mm)
Material:	Polycarbonate
Working Temp:	Max 75°C
Extra Info:	RoHS Compliant EMC approved



RoHS   

PRODUCT CODE	INPUT VOLTAGE	INPUT CURRENT	USAGE	IP RATING	DIMENSIONS
TRANS-60VA/PROL	220-240V 50Hz	0.27A	Indoor	IP 20	110 x 38 x 25mm