

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0444783111](#)
Status: **Active**
Overview: [Mini-Fit® Plus HCS](#)
Description: Mini-Fit® HCS Crimp Terminal, 16 AWG, Reel, Copper (Cu) Alloy, Tin (Sn)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-44478-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	44478
Application	Power
Comments	High Current
Crimp Quality Equipment	Yes
Overview	Mini-Fit® Plus HCS
Product Name	Mini-Fit®
UPC	800755527469

Physical

Gender	Male
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.133/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	16
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	11.0A
-------------------------------	-------


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-44478-001
Product Specification	RPS-44476-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

[44478](#) Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FineAdjust™ Applicator for Insulation OD 2.20-2.45mm, Optimized for 16 AWG Only	0639039400
FineAdjust™ Applicator for Insulation OD 1.80-2.20mm	0639015300

Optimized for 16 AWG Only FineAdjust™ Applicator for Insulation OD 2.60-3.15mm	<u>0639002800</u>
Optimized for 16 AWG Only Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	<u>0638190900</u>
T2 Terminator™ for insulation OD 2.20-2.45mm	<u>0639103000</u>
optimized for 16 AWG only Extraction Tool	<u>0011030044</u>
T2 Terminator™ for insulation OD 2.60-3.15mm optimized for 16 AWG only	<u>0639102800</u>

This document was generated on 07/06/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION