

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000067](#)
Status: **Active**
Overview: [Mini-Fit Jr.™ Power Connectors](#)
Description: [Mini-Fit® Male Crimp Terminal, Tin \(Sn\) over Phosphor Bronze, 22-28 AWG, Reel](#)

Documents:

[Drawing \(PDF\)](#) [Test Summary TS-5556-002 \(PDF\)](#)
[Product Specification PS-5556-002 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-5558-001 \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
Series [5558](#)
Application [Power](#)
Crimp Quality Equipment [Yes](#)
Overview [Mini-Fit Jr.™ Power Connectors](#)
Product Name [Mini-Fit®](#)
UPC [800754394024](#)

Physical

Durability (mating cycles max) [30](#)
Gender [Male](#)
Material - Metal [Phosphor Bronze](#)
Material - Plating Mating [Tin](#)
Material - Plating Termination [Tin](#)
Net Weight [0.120/g](#)
Packaging Type [Reel](#)
Plating min - Mating [0.889µm](#)
Plating min - Termination [0.914µm](#)
Termination Interface: Style [Crimp or Compression](#)
Wire Insulation Diameter [0.90-1.80mm](#)
Wire Size AWG [22, 24, 26, 28](#)
Wire Size mm² [N/A](#)

Electrical

Current - Maximum per Contact [9.0A](#)
Voltage - Maximum [600V](#)

Solder Process Data


Lead-freeProcess Capability [N/A](#)

Material Info

Old Part Number [5558-PBT2](#)

Reference - Drawing Numbers

Packaging Specification [PK-5558-001](#)
Product Specification [PS-5556-002](#)
Sales Drawing [SD-5558****](#)
Test Summary [TS-5556-002](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(2015 June 15): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[5558 Series](#)

Mates With

[5556 Mini-Fit® Crimp Terminal](#)

Use With

[5559 Mini-Fit Jr.™ Plug Housing](#), [30068 Mini-Fit® TPA Plug Housing](#), [42475 Mini-Fit® BMI Plug Housing](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

FineAdjust™
Applicator for
Insulation OD

Product #

[0639023800](#)

