

Pan Head Phillips - Metric D7985 M2x06 PA natural

01.47.126

Product No. 01.47.126

Type	Threaded Screws ISO
Thread	M2
Length	6.00 mm
Model	DIN 7985 / ISO 7085 Pan Head
Design	Cross Recess Phillips Drive
Material	Nylon 66 UL94 V-2
Plating	Natural
Head Dia.	4.00 mm
UL-Classification	UL94 V-2
Head Height	1.30 mm
RoHS II compliant	yes
Reach/SVHC free	yes

