

Hex-Standoff / Male - Female M4/SW7x25 Stainless Steel

05.14.259

Product No. 05.14.259

Model	Hex Male / Female
Length	25.00 mm
Thread 1 (Female)	M4
Inside Threadlength	9.00 mm
Outside Threadlength	8.00 mm
Material	Stainless steel 1.4305
Plating	Plain Finish
Wrench Size / Dia.	7 WS / Ø
Undercut	1
Thread 2 (Male)	M4
RoHS II compliant	yes
Reach/SVHC free	yes

