

## Hole Plugs with Truss Head / with Base Prong

14.14.140

Product No. 14.14.140

Type	Sealing Caps/Plugs
Model	Knock Out Seals
Design	flat, matt finish Head
Inside Diameter	5.50 mm
Height	Panel Thickness: 0.8 - 1.5 mm
Material	Nylon 6.6
Color	Black
Special	in Color natur avalably
Outside Dia.	10.30 mm
Hex Dim./ Dia.	0.00 mm
RoHS II compliant	yes
Reach/SVHC free	yes

Similar products Hole Plugs with Truss Head / 6.0/1,5;  
PA; natural  
14.14.141

