

MS-6 - Mid Span Slitter



Designed to provide easy access to optical fibers in loose buffer tubes 1.2mm - 3.3 mm diameter. With 6 precision grooves buffer tube slitting is done without damage to the fiber. The blades are replaceable.

Groove Sizes:

- 1.2 - 1.5 mm
- 1.5 - 1.8 mm
- 1.8 - 2.1 mm
- 2.1 - 2.5 mm
- 2.5 - 2.9 mm
- 2.9 - 3.3 mm

Easy to use:

1. Select the correct groove. Each groove is marked with the recommended fiber size
2. Place the fiber in the groove to be used. The arrow on the top of the MS-6 indicates blade location and pulling direction.
3. Close the tool making sure lock is engaged and pull

Cut Type	Slit
Cable Type	Loose Tube, Jacket
Cable Diameter	1.2-3.3 mm
Features	6 Precision grooves
Weight	0.14 lbs

Jonard Tools
134 Marbledale Road
Tuckahoe, NY 10707
Tel: 914.793.0700
Fax: 914.793.4527
mail: sales@jonard.com