

ProVue Slim Magnifying Lamp LED with Rolling Stand

Part no. 26507-SBK



Magnifying lamp with 45 high-performance SMD LEDs, a 2.25x (5-diopter) lens, and 32-inch spring-balanced arm mounted on a heavy-duty, weighted roller stand with five swivel casters for easy mobility.

Aven's ProVue Slim LED Magnifying Lamp, together with a heavy-duty floor stand that features a sturdy weighted base and five swivel casters, provides mobility and convenience for use in beauty salons, medical offices and hobby applications. The 30-inch pole height is ideal for standing or seated inspection. ProVue Slim's magnifier, which features 45 high-performance SMD LED lights and a 4.75-inch crystal clear 5-diopter (2.25x) glass lens, provides 360° distortion-free viewing. The slender and durable ABS plastic housing, with integrated handle for quick positioning, mounted to a 32-inch spring-balanced arm stays set securely in any position.

Features:

- 45 high performance energy saving LED for shadow free illumination
- 4.75"(120mm)-2.25x (5 Diopter) crystal clear glass lens for 360 degree distortion-free viewing
- 32" (812mm) spring balanced arm stays put in any position
- 5 full swivel castors for easy mobility
- Designed for durability

Specifications:

Magnification	5 Diopter (2.25x)
Lens Diameter	4.75" (120mm)
Focal Length	8" (206mm)
Adjustable Arm Length	32" (812mm)
Color	White
Lighting	45 SMD LEDs
LED Life	Minimum 20,000 hours
Watts	9.4
Base Dimensions	5 cross bars each 216mm in length mounted to a center plate 178mm (7in) in diameter.
Post height	780mm (30in)
Post inner diameter	11.5mm
Package Contents	ProVue Slim LED Magnifying Lamp - White, LED, 5-Diopter, Base with weight, 5 cross bars and 5 castors with hardware for assembly
Magnifying Lamp Accessories	26501-SLA Swing Away Lens-5 Diopter (2.25x)
Weight	21.9 lb