


INTERCONNECTION

Pluggable Terminal Strips Plug in Style

- Moulded in natural PA6, self extinguishing to UL94-V2 or white PA6.6, self extinguishing to UL94-V0
- Easily cut to size
- Available pre-cut to length
- CE Approved



SPECIFICATION


Voltage (max)	450V AC
Working temperature	110°C
No. of poles	12
Moulding	UL94-V2 Self extinguishing PA6 UL94-V0 Self extinguishing PA6.6
Conducting bush	Nikel plated brass
Screws	Zinc, plated steel

UL94-V2 Material

TYPE NO.	SIZE / RATING	INSERT DIAMETER	TERMINAL SCREWS	LENGTH	WIDTH	HEIGHT	PITCH	FIXING HOLE DIAMETER	MAX CURRENT
CTSN431/12MF	8mm/6A	2.9mm	M3	94mm	16mm	15.5mm	8mm	2.75mm	17.5A
CTSN433/12MF	10.25mm/10A	3.4mm	M3	119.4mm	20.5mm	16.4mm	10.25mm	3.2mm	24A
CTSN434/12MF	12.5mm/16A	4.3mm	M3.5	143mm	23.5mm	19mm	12.3mm	3.5mm	57A



UL94-V0 Material

TYPE NO.	SIZE / RATING	INSERT DIAMETER	TERMINAL SCREWS	LENGTH	WIDTH	HEIGHT	PITCH	FIXING HOLE DIAMETER	MAX CURRENT
CTSN631/12MF	8mm/6A	2.9mm	M3	94mm	16mm	15.5mm	8mm	2.75mm	17.5A
CTSN633/12MF	10.25mm/10A	3.4mm	M3	119.4mm	20.5mm	16.4mm	10.25mm	3.2mm	24A
CTSN634/12MF	12.5mm/16A	4.3mm	M3.5	143mm	23.5mm	19mm	12.3mm	3.5mm	57A



Strain relief

- Clamps external conductors in lighting fixtures according to EN 60598
- Natural colour PA6
- Takes the strain on the wires
- Prevents conductors from twisting
- Protects wire coating from abrasion and friction



TYPE NO.	TERMINAL STRIP	LENGTH	WIDTH	HEIGHT
CSR1	CTSN431	49.5mm	31mm	22.5mm
CSR2	CTSN433 / CTSN433T	52.5mm	31mm	22.5mm
CSR3	CTSN434	54.5mm	31mm	22.5mm

