



**IP66\***  
 SUITABILITY

**Low Profile NPT Cord Connectors**

NPT Hub Size	Cord Diameter Inches	(mm)	Color	Catalog Number	Non-metallic Locknuts
3/8	.18"-.31"	(4.6-7.9)	Gray	<b>SEC38GA*</b>	<b>31622002LPK50</b>
3/8	.18"-.31"	(4.6-7.9)	Black	<b>SEC38BA*</b>	<b>31622002LPK50</b>
1/2	.17"-.45"	(4.3-11.4)	Gray	<b>SEC50GA</b>	<b>31622003LPK50</b>
1/2	.17"-.45"	(4.3-11.4)	Black	<b>SEC50BA</b>	<b>31622003LPK50</b>
3/4	.45"-.71"	(11.4-18.0)	Gray	<b>SEC75GA</b>	<b>31622007LPK50</b>
3/4	.45"-.71"	(11.4-18.0)	Black	<b>SEC75BA</b>	<b>31622007LPK50</b>
1	.59"-1.00"	(15-25.4)	Gray	<b>SEC100GA</b>	<b>31622008LPK50</b>
1	.59"-1.00"	(15-25.4)	Black	<b>SEC100BA</b>	<b>31622008LPK50</b>



**SEC100BA**

Note: See pages V-87 to V-95 for technical information and dimensional drawings.  
 Catalog numbers with "PK50" suffix are bulk packed 50 pieces.

**Low Profile PG<sup>Δ</sup> Cord Connectors**

Hub Size	Cord Diameter Inches	(mm)	Color	Catalog Number	Non-metallic Locknuts
PG7	.11"-.25"	(2.9-6.4)	Gray	<b>SECP7GA*</b>	<b>LNP7BPK100</b>
PG7	.11"-.25"	(2.9-6.4)	Black	<b>SECP7BA*</b>	<b>LNP7BPK100</b>
PG9	.18"-.31"	(4.6-7.9)	Gray	<b>SECP9GA*</b>	<b>LNP9BPK100</b>
PG9	.18"-.31"	(4.6-7.9)	Black	<b>SECP9BA*</b>	<b>LNP9BPK100</b>
PG11	.23"-.40"	(5.8-10.0)	Gray	<b>SECP11GA*</b>	<b>LNP11BPK100</b>
PG11	.23"-.40"	(5.8-10.0)	Black	<b>SECP11BA*</b>	<b>LNP11BPK100</b>
PG13.5	.17"-.47"	(4.3-11.9)	Gray	<b>SECP13GA</b>	<b>LNP13BPK100</b>
PG13.5	.17"-.47"	(4.3-11.9)	Black	<b>SECP13BA</b>	<b>LNP13BPK100</b>
PG16	.23"-.53"	(5.8-13.5)	Gray	<b>SECP16GA</b>	<b>LNP16BPK100</b>
PG16	.23"-.53"	(5.8-13.5)	Black	<b>SECP16BA</b>	<b>LNP16BPK100</b>
PG21	.45"-.71"	(11.4-17.9)	Gray	<b>SECP21GA</b>	<b>LNP21BPK100</b>
PG21	.45"-.71"	(11.4-17.9)	Black	<b>SECP21BA</b>	<b>LNP21BPK100</b>
PG29	.59"-.99"	(15-25.2)	Gray	<b>SECP29GA</b>	<b>LNP29BPK25</b>
PG29	.59"-.99"	(15-25.2)	Black	<b>SECP29BA</b>	<b>LNP29BPK25</b>
PG36	.88"-1.30"	(22.2-32.0)	Gray	<b>SECP36GA</b>	<b>LNP36BPK25</b>
PG36	.88"-1.30"	(22.2-32.0)	Black	<b>SECP36BA</b>	<b>LNP36BPK25</b>



**SECP29GA**

**Low Profile Metric Cord Connectors**

Hub Size	Cord Diameter Inches	(mm)	Color	Catalog Number	Non-metallic Locknuts
M12	.12"-.25"	(2.9-6.4)	Gray	<b>SECM12G</b>	<b>LNM12BPK100</b>
M12	.12"-.25"	(2.9-6.4)	Black	<b>SECM12B</b>	<b>LNM12BPK100</b>
M16	.11"-.31"	(2.7-7.9)	Gray	<b>SECM16G</b>	<b>LNM16BPK100</b>
M16	.11"-.31"	(2.7-7.9)	Black	<b>SECM16B</b>	<b>LNM16BPK100</b>
M20	.17"-.45"	(4.3-11.4)	Gray	<b>SECM20G*</b>	<b>LNM20BPK100</b>
M20	.17"-.45"	(4.3-11.4)	Black	<b>SECM20B*</b>	<b>LNM20BPK100</b>
M25	.49"-.71"	(12.3-18.0)	Gray	<b>SECM25G*</b>	<b>LNM25BPK100</b>
M25	.49"-.71"	(12.3-18.0)	Black	<b>SECM25B*</b>	<b>LNM25BPK100</b>
M32	.59"-1.00"	(15.0-25.4)	Gray	<b>SECM32G*</b>	<b>LNM32BPK100</b>
M32	.59"-1.00"	(15.0-25.4)	Black	<b>SECM32B*</b>	<b>LNM32BPK100</b>
M40	.87"-1.30"	(22.0-32.0)	Gray	<b>SECM40G</b>	<b>LNM40BPK100</b>
M40	.87"-1.30"	(22.0-32.0)	Black	<b>SECM40B</b>	<b>LNM40BPK100</b>



**LNP29BPK25**

Note: See pages V-87 to V-96 for technical information and dimensional drawings.  
 Catalog numbers above with "PK100" suffix, i.e. LNP7BPK100, are bulk packed 100 per carton.  
 Catalog numbers above with "PK25" suffix, i.e. LNP29BPK25, are bulk packed 25 per carton.  
 \*Items indicated are UL recognized components.  
 ΔPanzergewinde.