



**20A 125/250V AC**  
 NEMA L14-20R  
 UL/CSA  
 2 (1) HP



**20A 3Ø 250V AC**  
 NEMA L15-20R  
 UL/CSA  
 3 HP



**20A 3Ø 480V AC**  
 NEMA L16-20R  
 UL/CSA  
 5 HP

## Connector Bodies

### Watertight Safety-Shroud®

IP66 SUITABILITY    UL Type 4x, 12

| Description                                | Cord Dia.              | Catalog Number   |                  |                  |
|--|------------------------|------------------|------------------|------------------|
| Black Valox® housing, white Valox® clamps. | .350"-1.150"<br>(9-29) | <b>HBL2413SW</b> | <b>HBL2423SW</b> | <b>HBL2433SW</b> |




**HBL2423SW**

### Insulgrip®

IP20 SUITABILITY

| Description                        | Cord Dia.              | Catalog Number   |                  |                  |
|------------------------------------|------------------------|------------------|------------------|------------------|
| Black and white nylon.             | .350"-1.150"<br>(9-29) | <b>HBL2413</b>   | <b>HBL2423</b>   | <b>HBL2433</b>   |
| Corrosion resistant, yellow nylon. | .350"-1.150"<br>(9-29) | <b>HBL24CM13</b> | <b>HBL24CM23</b> | <b>HBL24CM33</b> |
| All black nylon.                   | .350"-1.150"<br>(9-29) | <b>HBL2413BK</b> | -                | -                |



**HBL2413**

Note: See page B-53 for accessories.

## Receptacles

### Watertight Safety-Shroud®

IP66 SUITABILITY    UL Type 4x, 12

| Description                                 | Catalog Number   |                  |                  |
|---|------------------|------------------|------------------|
| Gray Valox® housing and flange, back wired. | <b>HBL2410SW</b> | <b>HBL2420SW</b> | <b>HBL2430SW</b> |


Note: See page B-54 for accessories.

### Safety-Shroud® Twist-Lock®

IP20 SUITABILITY

| Description   | Catalog Number    |                   |                   |
|---|-------------------|-------------------|-------------------|
| Gray Valox® angle housing, one gang, back wired.    | <b>HBL2410AR</b>  | <b>HBL2420AR</b>  | <b>HBL2430AR</b>  |
| Gray Valox® surface mounting, one gang, back wired. | <b>HBL2410SR</b>  | <b>HBL2420SR</b>  | <b>HBL2430SR</b>  |
| Gray Valox® semi-flush, two gang, back wired.       | <b>HBL2410SR2</b> | <b>HBL2420SR2</b> | <b>HBL2430SR2</b> |

Note: See page B-54 for accessories.




**HBL2420SW**

### Single Flush Receptacles

IP20 SUITABILITY

| Description  | Catalog Number   |                  |                |
|--|------------------|------------------|----------------|
| Black nylon face, back and side wired.                   | <b>HBL2410</b>   | <b>HBL2420</b>   | <b>HBL2430</b> |
| Isolated ground, orange nylon face, back and side wired. | <b>IG2410</b>    | <b>IG2420</b>    | -              |
| Ring terminal connection.                                | <b>HBL2410RT</b> | <b>HBL2420RT</b> | -              |

Note: See page B-52 for accessories.



**HBL2420AR**


### Insulgrip® Flanged Receptacles

| Description               | Catalog Number |                |                |
|---------------------------|----------------|----------------|----------------|
| Nylon casing, back wired. | <b>HBL2416</b> | <b>HBL2426</b> | <b>HBL2436</b> |


Note: See page B-52 for accessories.




**HBL2416**



**HBL2410**



**HBL2420SR2**



**HBL2420SR**

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.

Dimensions in Inches (mm)