









# Wiha Torque Control Blade & Handle Reference Chart

Wiha Blade Number	Torque Blade Style & Tip Size	Max Recommended Torque Newton Meters	Max Recommended Torque In Inch Lbs.	Adjustment Range Handle Inch Lbs	TorqueVario Handle Number
<b>Phillips</b> 					
Blade No	Tip Size	Newton Meters	Inch Lbs.	Handle Inch Lbs	Handle Number
28540	Phillips 000	0.4	3.5	1 to 5	28501
28541	Phillips 00	0.9	8.0	5 to 10	28502
28542	Phillips 0	3.8	33.6	10 to 50	28506
28543	Phillips 1	5.5	48.6	20 to 70	28508
<b>Slotted</b> 					
Blade No	Tip Size	Newton Meters	Inch Lbs.	Handle Inch Lbs	Handle Number
28534	Slotted 1.5	0.15	1.3	1 to 5	28501
28535	Slotted 2.0	0.4	3.5	1 to 5	28501
28536	Slotted 2.5	0.4	3.5	1 to 5	28501
28537	Slotted 3.0	0.6	5.3	5 to 10	28502
28538	Slotted 3.5	1.1	9.7	7.5 to 20	28504
28539	Slotted 4.0	2.5	22.1	10 to 50	28506
<b>Hex Metric</b> 					
Blade No	Tip Size	Newton Meters	Inch Lbs.	Handle Inch Lbs	Handle Number
28545	Hex 1.5	0.9	8.0	5 to 10	28502
28546	Hex 2.0	1.8	15.9	7.5 to 20	28504
28547	Hex 2.5	3.8	33.6	10 to 50	28506
28548	Hex 3.0	6.6	58.3	20 to 70	28508
28549	Hex 4.0	8	70.7	20 to 70	28508
<b>Hex Inch</b> 					
Blade No	Tip Size	Newton Meters	Inch Lbs.	Handle Inch Lbs	Handle Number
28555	Hex .050	0.4	3.5	1 to 5	28501
28556	Hex 1/6	0.9	8.0	5 to 10	28502
28557	Hex 5/64	1.8	15.9	7 to 20	28504
28558	Hex 3/32	1.9	16.8	10 to 50	28506
28559	Hex 7/64	3.8	33.6	20 to 70	28508
28560	Hex 1/8	5.5	48.6	20 to 70	28508
28587	Hex 9/64	7.2	63.6	20 to 70	28508
28588	Hex 5/32	8	70.7	20 to 70	28508
<b>Torx</b> 					
Blade No	Tip Size	Newton Meters	Inch Lbs.	Handle Inch Lbs	Handle Number
28561	Torx T5	0.4	3.5	1 to 5	28501
28562	Torx T6	0.6	5.3	5 to 10	28502
28563	Torx T7	0.9	8.0	5 to 10	28502
28564	Torx T8	1.3	11.5	7.5 to 20	28504
28565	Torx T9	2.5	22.1	10 to 50	28506
28566	Torx T10	3.8	33.6	10 to 50	28506
28567	Torx T15	5.5	48.6	10 to 50	28506
28568	Torx T20	8	70.7	20 to 70	28508
28569	Torx T25	8	70.7	20 to 70	28508
<b>Torx Plus</b> 					
Blade No	Tip Size	Newton Meters	Inch Lbs.	Handle Inch Lbs	Handle Number
28571	Torx Plus IP5	0.5	4.4	1 to 5	28501
28572	Torx Plus IP6	0.8	7.1	5 to 10	28502
28573	Torx Plus IP7	1.3	11.5	7.5 to 20	28504
27574	Torx Plus IP8	2	17.7	7.5 to 20	28504
28575	Torx Plus IP9	3	26.5	10 to 50	28506
28576	Torx Plus IP10	4.5	39.8	10 to 50	28506
28577	Torx Plus IP15	6.6	58.3	20 to 70	28508
28578	Torx Plus IP20	8	70.7	20 to 70	28508
28579	Torx Plus IP25	8	70.7	20 to 70	28508