

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0830009502](#)
Status: **Active**
Overview: [Commercial Micro-D High-Density Connectors](#)
Description: [Commercial Micro-D Socket Terminal, 5,000 per Reel](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	83000
Application	Signal
Crimp Quality Equipment	Yes
Overview	Commercial Micro-D High-Density Connectors
Product Name	Commercial Micro-D
UPC	800753013766

Physical

Gender	Female
Material - Metal	Beryllium Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	280.090/mg
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.75mm max.
Wire Size AWG	26, 28
Wire Size mm ²	N/A

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contains SVHC(2015
June 15): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[83000 Series](#)

Use With

83611 , 83619 , 83612 , 83614

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0638114800
T2 Terminator Die	0638522000
FineAdjust™ Applicator	0638622000

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION