

Vertical UK PDU

Picture shows V13A/10

- Vertical UK BS1363 right-angled outlets
- Tough aluminium extrusion
- Shrouded switch and switch cover
- C14, C20, or 16A commando options
- 3m 1.5mm cable

Vertical UK PDUs are widely used to accommodate cabinets where a higher number of UK sockets are needed, but rack space is also at a premium. Being mounted at the back of the cabinet means that the PDU maintains a '0U' profile, allowing the rest of the cabinet to be populated with critical hardware.

Standard products

Order Code	Product Description
V13A/4	4-way UK 13A power with switch to 3-metre lead to 13A plug
V13A/5	5-way UK 13A power with switch to 3-metre lead to 13A plug
V13A/6	6-way UK 13A power with switch to 3-metre lead to 13A plug
V13A/8	8-way UK 13A power with switch to 3-metre lead to 13A plug
V13A/8/F	8-way UK filtered power with switch to 3-metre lead to 13A plug
V13A/10	10-way UK 13A power with switch to 3-metre lead to 13A plug
V13A/10/F	10-way UK filtered power with switch to 3-metre lead to 13A plug
V13A/12	12-way UK 13A power with switch to 3-metre lead to 13A plug
V13A/12/F	12-way UK filtered power with switch to 3-metre lead to 13A plug
V13A/16	16-way UK 13A power with switch to 3-metre lead to 13A plug


PDU options



IEC C14 plug
IEC 60320(320)



16A commando plug
IEC 60309(309)



IEC C20 plug
IEC 60320(320)

PDU technical data

Weight of PDU	0.95kg – 1.9kg
Net length of PDU	490mm – 1090mm
Net width of PDU	60mm
Net depth of PDU	45mm
Shipping length of PDU	515mm – 1120mm
Shipping Width of PDU	150mm
Shipping Depth of PDU	70mm
Shipping Weight of PDU	1.1kg – 2.4kg
PDU max power	3250W
Output rating	13A
Overall rating	16A
Input Frequency	50/60Hz
Acceptable Input Voltage	250VAC

