

## ESP-130/WS - PA Wall Speaker

100V



**These wall speakers impress by an extraordinarily flat design which is only achieved by applying the latest NEODYMIUM magnetic systems.**

**The ESP-130... speaker systems already provide a very pleasant and complete sound and yet, with a total depth of only 38 mm, they are of such a flat design, that they are just as unobtrusive on the wall as a flush-mount speaker. PA wall speaker**

- 100 V line technique via audio transformer with 2.5 W and 5 W power taps
- 2-way system with neodymium bass-midrange speaker and dome tweeter
- White plastic cabinet with protective metal grille
- Slimline design for unobtrusive wall mounting



## Technical Data

Frequency range	: 80-18,000 Hz
Power capability, 100 V	: 5/2.5 W <sub>RMS</sub>
Power capability, 8 Ohm	: -
SPL (1 W/m)	: -
Max. rated SPL	: -
Type of speaker	: -
Mounting cutout	: -
Mounting depth	: -
Admiss. ambient temp.	: 0-40°C
Dimensions	: 185x275x38 mm
Weight	: 1.2 kg
Other features	: -