

MMX-4 - Microphone Mixer



Miniature microphone mixer

- 4 mono microphone channels
- Output level control, peak LED
- Supplied without battery



Technical Data

General Information

Input sensitivity	:
Mic	: 5 mV
Line	:
Outputs	: 100 mV
Frequency range	: 20-20,000 Hz
THD	: < 0.5 %
S/N ratio	: 55 dB
Power supply	: 9 V battery or via optional PSU PSS-600E
Admiss. ambient temp.	: 0-40 °C
Dimensions	: 148x85x55 mm
Weight	: approx. 500 g
Inputs	: 4 x 6.3 mm jack
Outputs	: 1 x 6.3 mm jack
Power supply	: 1 x low-voltage jack