

AHD 1.0



HD 720P 8-Camera Hybrid DVR

Model: OAHD-D8

HD 720P 8-Camera Hybrid (HD 720P, HD 960H) DVR

- HD 960H @ 25fps, HD 720P @ 15fps
- 4 Audio Inputs
- Remote Access via Smartphone, Tablet, PC & Mac
- Email Alerts
- VGA, BNC & HDMI Monitor Outputs
- Front Panel, Mouse or IR Remote Control
- Supports 8x HD 720P Cameras / 4x HD 960H & 4x HD 720P / 8x HD 960H Cameras



Features

The OAHD-D8 8 channel DVR is the latest from Y3K and offers High Definition HD 720P real time recording. The DVR presents great value for money and has both VGA and HDMI outputs. The model has multiple alarm record modes, supporting HDD and video input alarm management. Backing up files is quick and easy with the built-in USB port.

The OAHD-D8 provides recording in HD 960H, and HD 720P in real time and supports PTZ camera operation through RS-485. For easy control and setup, the DVR features an On Screen Display (GUI) and can be controlled by the new touch panel function, Remote Control or Mouse.

Technical Specifications

OAHD-D8	
Brand	Unbranded
Description	8-Camera Hybrid DVR
Video Compression	H.264
Video System	NTSC / PAL
Video Input / Output	8 CH Input / 1 CH Output (1x BNC, 1x VGA, 1x HDMI)
Sport Output	No
Audio Input / Output	4 CH Input / 1 CH Output
Display Resolution	PAL: 960x576 / 1280x720 @ 25fps
Display Feature	Single, Quad, S.E.Q
Recording Resolution	PAL: 960x576 (HD 960H), 1280x720 (HD 720P)
Recording Speed	PAL: 960H Mode & 720P Mode: 15fps
Recording Mode	Continuous / Manual / Motion Detection
Playback Channel	1 / 4 CH
Playback Speed	PAL: 960H Mode / 720P Mode: 15fps
DVD-RW	No
Sensor & Alarm I/O	No
IR Extender Port	No
Network	Lan, DHCP, Dynamic IP & DDNS
HDD Interface	1 SATA HDD, up to 4TB
Multiplex Operation	Live Display, Record, Playback, Backup & Network
USB	2x USB (For mouse and Backup / Upgrade)
PTZ Control	Yes
Mobile Surveillance	N_Eye - Android & iOS
CMS Software	Yes
Web Browser	Internet Explorer, Safari, Chrome, Firefox
Video Output	VGA: 800x600, 1024x768, 1280x1024, 1440x900, 1920x1080 HDMI: 1080P
Power Supply	DC 12V 2000mA
Fan	No
Remote Control	Yes
Rack Mount Size (U)	1
Dimensions (WxHxD)	255x42x220mm

All specifications shown are subject to change without notice, please confirm up to date details when ordering. All network specifications and recording times are based upon theoretical scenarios.

Actual performances will vary depending on external factors. No liability will be accepted by Y3K for any errors or omissions in this information. All relevant trade marks acknowledged.
© Y3K (Europe) Limited 2015

■ DISTRIBUTED BY



Y3K (EUROPE)

Unit 2 Valley Point, Beddington Farm Road, Croydon, Surrey, CR0 4WP
Tel: 0208 689 9999 Fax: 0871 222 143 Web: www.y3k.com