






# Female Disconnects – Nylon Fully Insulated with Insulation Grip Interlock Barrel



Product Number <sup>†</sup>	UPC (054007-)	Wire Range (AWG)	Mates with Male Tab Width(W) x Thickness	L	Barrel Length	Barrel I.D.	Maximum Insulation Diameter	Terminals per:	
								Carton	Case
MNGI18-187DFIX	09984	22-18	0.187 x 0.020	0.81	0.25	0.080	0.145	100	500
MNGI18-187DFIK	69566	22-18	0.187 x 0.020	0.81	0.25	0.080	0.145	—	1000
MNGI18-250DFIX	09985	22-18	0.250 x 0.032	0.87	0.25	0.076	0.145	100	500
MNGI18-250DFIK	69567	22-18	0.250 x 0.032	0.87	0.25	0.076	0.145	—	1000
MNGI14-187DFIX	09982	16-14	0.187 x 0.020	0.81	0.25	0.080	0.145	100	500
MNGI14-187DFIK	69564	16-14	0.187 x 0.020	0.81	0.25	0.080	0.145	—	1000
MNGI14-250DFIX	09983	16-14	0.250 x 0.032	0.87	0.25	0.076	0.145	100	500
MNGI14-250DFIK	69565	16-14	0.250 x 0.032	0.87	0.25	0.076	0.145	—	1000
MNGI10-250DFIX	09981	12-10	0.250 x 0.032	0.99	0.25	0.128	0.250	50	500
MNGI10-250DFIK	69563	12-10	0.250 x 0.032	0.99	0.25	0.128	0.250	—	500



**Wire Range**  
Suggested Mate

**MNGI18-187DFI**  
22-18  
MNG18-187DMI

**MNGI18-250DFI**  
22-18  
MNG18-250DMI

**MNGI14-187DFI**  
16-14  
MNG14-187DMI

**MNGI14-250DFI**  
16-14  
MNG14-250DMI

**MNGI10-250DFI**  
12-10  
MNG10-250DMI