

KEMET Part Number: PME271MD6220KR30
(P276SP224K275A)

Capacitor, film, 0.22 uF, +/-10% Tol, -40/+110C, Safety: X2, 275 VAC, Lead Spacing=22.5 mm



Dimensions (mm)

Symbol	Dimension	Tolerance
L	27	MAX
H	19	MAX
T	10	MAX
S	22.5	+/-0.5
LL	30	+5
F	0.8	NOM

Packaging Specifications

Package Kind:	Bulk
Package Quantity:	150

General Information

Supplier:	KEMET
Dielectric:	Metallized Paper
Application:	Safety: X2
Style:	Radial Molded
Lead Form:	Wire Leads
Approvals:	ENEC,UL,cUL
RoHS:	Yes

Specifications

Capacitance:	0.22 uF
Voltage:	630 VDC
Tolerance:	+/-10%
Voltage AC:	275 VAC
Rated Temperature:	110C
Temperature Range:	-40/+110C
Dissipation Factor @ 1 kHz:	1.3%
Insulation Resistance:	12 GOhm
Maximum dVdT:	600 v/us
Miscellaneous:	SRF= 2.6 MHz