

**KEMET Part Number: SMC12.7 155J50B31 TR24**  
(F125YR155J050V, SMC100ZB7150JB31T1)

Capacitor, film, 1.5 uF, +/-5% Tol, General Purpose, 50 VDC@125C



Note: '()' correspond to the letters used in the product bulletin

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	12.7	+/-0.2
W	11.5	+/-0.2
T	6.5	+/-0.2
F	0.5	NOM

Packaging Specifications	
Package Kind:	T&R
Package Size:	Standard
Package Quantity:	600

General Information	
Supplier:	KEMET
Dielectric:	Metallized PPS
Application:	General Purpose
Sub Application:	HighStability
Style:	Surface Mount
Chip Size:	5045
RoHS:	Yes

Specifications	
Capacitance:	1.5 uF
Voltage:	50 VDC
Tolerance:	+/-5%
Voltage AC:	30 VAC
Rated Temperature:	125C
Temperature Range:	-55/+125C
Dissipation Factor @ 1 kHz:	0.15%
Dissipation Factor @ 10 kHz:	0.3%
Insulation Resistance:	3.33 GOhm
Maximum dVdT:	3 v/us