

HEAVY DUTY ENCLOSURES

91 Series IP67 Low Profile Cases

Beautifully designed low profile IP67 waterproof enclosures, ideal for tracking/monitoring in harsh environments.

- IP67 rated, perfect for outdoor applications
- White enclosures made from ASA UL94-HB plastic for high ultraviolet resistance
- Dark Grey enclosures made from ABS UL94-V0 plastic for high flammability rating
- Wall mount holes behind hinged caps for superior aesthetic finish
- Mount Kit accessory for easy mounting to poles, pillars, posts and lamp posts


TAKACHI



SPECIFICATION

Material:	
Dark grey	Lid & base ABS UL94-V0
White grey	Lid & base ASA UL94-HB
Operating Temperature	
-10°C to +60°C	
Standard colours	
Dark grey or white grey	
Standard unit includes	
Lid, base, gasket & fixing screws	

DARK GREY	WHITE GREY	LENGTH	WIDTH	HEIGHT
WP9-13-3C	WP9-13-3G	130mm	90mm	25mm
WP9-13-4C	WP9-13-4G	130mm	90mm	40mm
WP10-10-3C	WP10-10-3G	100mm	100mm	25mm
WP10-10-4C	WP10-10-4G	100mm	100mm	40mm
WP11-15-3C	WP11-15-3G	150mm	110mm	27mm
WP11-15-4C	WP11-15-4G	150mm	110mm	40mm



Rubber Feet

PART NO.	LENGTH	WIDTH	HEIGHT
PFF-M2.5D	10mm	10mm	7.5mm



Pole Mount Kit

PART NO.	LENGTH	WIDTH	HEIGHT	DESCRIPTION
WPMB-M4D	28mm	18mm	12mm	POLE MOUNT KIT, DARK GREY
WPMBM4G	28mm	18mm	12mm	POLE MOUNT KIT, WHITE GREY