

Perforated panels

Perfo-Stor™ and wall panels

• = In stock products

The perforated back panels are attached to the slotted uprights. The perforated wall panels are attached, either directly to the wall or to the slotted

uprights with attachment clips. The size of the perforation is .35 x .35 inches, center to center 1.49 inches.



1 Perforated back panels

name	module	W x H inches	order No
Perforated back panel	M20	18.50 x 11.81	860951-35 •
Perforated back panel	M20	18.42 x 15.31	861501-35
Perforated back panel	M30	28.97 x 7.63	861510-07 •
Perforated back panel	M30	28.26 x 15.31	861511-35 •
Perforated back panel	M30	28.97 x 25.19	861512-35 •
Perforated back panel	M30	28.97 x 25.19	861512-07 •
Perforated back panel	M30	28.97 x 39.48	861514-35 •
Perforated back panel	M30	28.97 x 39.48	861514-07 •
Perforated back panel	M30	28.26 x 24.13	861512-35 •
Perforated back panel	M30	28.26 x 24.13	861512-07 •
Perforated back panel, insulated	M30	28.26 x 24.13	861701-35
Perforated back panel, insulated	M30	28.26 x 24.13	861701-07
Perforated back panel	M36	34.29 x 24.13	861517-35 •
Perforated back panel	M36	34.29 x 15.31	861516-35 •
Perforated back panel 39.37		38.81 x 37.79	861535-07
Perforated back panel	M48	47.25 x 15.35	E816427-35
Perforated back panel	M53	51.88 x 15.35	861521-35
Perforated back panel	M60	58.03 x 15.35	861526-35
Perforated back panel	M72	69.84 x 15.35	861531-35

Perforated wall panels attached to the wall

name	W x H inches	order No
Perforated wall panel	17.87 x 38.89	837369-07
Perforated wall panel	37.36 x 38.89	852145-07
Perforated wall panel	37.36 x 56.85	837342-07
Perforated wall panel	37.36 x 77.79	837350-07 •


Attach directly to the wall using screws.

2 Back panels

name	module	W x H inches	order No
Back panel	M20	19.09 x 9.44	860801-35
Back panel	M20	19.09 x 15.74	860802-35
Back panel	M20	19.09 x 25.19	860803-35
Back panel	M30	28.93 x 9.44	861550-35
Back panel	M30	28.93 x 15.74	861551-35 •
Back panel	M30	28.93 x 25.19	861552-35 •
Back panel	M30	28.93 x 25.19	861552-07
Back panel	M36	34.96 x 15.74	861556-35 •
Back panel	M36	36 x 25.19	E802913-35 •

Back panels are solid, color light grey ESD 35 (ESD 7035).

The color code is included in the order number. It is either at the end, following the hyphen (e.g. 860804-**35**), or in the middle (e.g. 100/40/200 C334**07**000).



Tackable Backscreens

name	module	W x H inches	color	order No
Backscreen fabric with metal panel	M30	24.13 x 28	crimson red	14-9803509 •
Backscreen fabric with metal panel	M30	24.13 x 28	dove grey	14-9803510
Backscreen fabric with metal panel	M30	24.13 x 28	navy blue	14-9803511 •
Backscreen fabric with metal panel	M36	24.13 x 34	crimson red	14-9803513 •
Backscreen fabric with metal panel	M36	24.13 x 34	dove grey	14-9803514
Backscreen fabric with metal panel	M36	24.13 x 34	navy blue	14-9803515 •