


7W LED FULL LANTERN / WITH PIR

• This luminaire contains built-in LED lamps and the lamps cannot be changed in the luminaire

Code	Version	Colour	Wattage	Colour Temp.	Lumens	Avg. Rated Life (Hrs)	IP Rating	Energy Rating
FULLBK	Standard	Black	7W	3100K	310 lm	35,000 hrs	IP44	A
FULLPIRBK	PIR	Black	7W	3100K	310 lm	35,000 hrs	IP44	A



This luminaire contains built-in LED lamps.



The lamps cannot be changed in the luminaire.

874/2012



LAMP SPECIFICATIONS:

Lumens total flux	310 lm
Lumens 120° flux	280 lm
Rated Wattage	7W
Rated luminous flux	280 lm
Nominal life time of the lamp	35,000 hrs
Colour temperature	3100K
Number of switching cycles before premature lamp failure	≥15,000
Warm-up time up to 60 % of the full light output	Instant full light
Dimmable	No
LED array dimensions (Ø)	110mm
Nominal beam angle	120°
Rated power	7W
Rated lamp lifetime	35,000 hrs
Lamp power factor	>0.5s
Lumen maintenance factor at end of nominal life	≥0.70
Starting time	<0.1s
Colour rendering	≥80
Colour consistency	Within 6 step Macadam ellipse
Rated peak intensity	110cd
Rated beam angle	120°
Voltage	240V

Not suitable for accent lighting