





Subracks - *europac*PRO ServicePLUS

Guide rails type "accessory", one-piece,
groove width 2 mm and 2.5 mm

Order Information

Assembly - can be clipped into Al extruded horizontal rails - can be clipped into 1.5 mm thick plates Storage temperature from -40 °C ... +130 °C			accessory type		Guide rails		accessory type, strengthened	for heavy modules, Al extrusion, silver, robust version
			 <p>up to 280 mm length, PBT, UL 94 V-0; > 280 mm length, multi-piece, end piece PBT, UL 94 V-0, middle section Al extrusion</p>		 <p>PBT UL 94 V-0, red; support beam of guide rails adds to strengthening</p>		 <p>Al extrusion; is screwed to horizontal rail "heavy" with retention screws</p>	
Board length mm	Groove width mm	Colour	PU 10 pieces ²⁾	1 piece (SPQ 50)	1 piece (SPQ 50)	1 piece (SPQ 50)	1 piece (SPQ 10) ¹⁾	
100	2	red	–	64560-082	–	–	–	
160	2	red	24560-373	64560-005	64560-076	–	–	
160	2	grey/silver	–	64560-055	–	–	34562-881	
220	2	red	24560-374	64560-006	64560-078	–	–	
220	2	grey/silver	–	64560-166	–	–	34562-882	
280	2	red/silver	24560-375	–	64560-080	–	34562-883	
340	2	red/silver	24560-376	–	–	–	34562-884	
400	2	red/silver	–	–	–	–	34562-885	
160	2.5	silver	–	–	–	–	34564-881	
220	2.5	silver	–	–	–	–	34564-882	
280	2.5	silver	–	–	–	–	34564-883	
340	2.5	silver	–	–	–	–	34564-884	
400	2.5	silver	–	–	–	–	34564-885	

Accessories

Retention screw, PU 100 pieces; torque max. 0.2 Nm 	24560-141	24560-141	24560-141	24560-157
ESD clip, PU 50 pieces	24560-255	24560-255	24560-255	–
Board locking, red, PU 10 pieces	24560-377	24560-377	24560-377	–
Board handle, red, PU 10 pieces	24560-378	24560-378	24560-378	–
Identification strips for board handle, red, PU 1 sheet = 438 pieces	60817-228	60817-228	60817-228	–
Coding see page		6.41		–

1) SPQ (standard pack quantity): Part number includes 1 piece, but delivery is exclusively made in standard pack quantity (SPQ); please order at least the SPQ quantity or a multiple

2) Part no. includes one packing unit (PU); delivery is exclusively made in PU