

PRO-ELEC

INSTRUCTION MANUAL

6 INCH DESK FAN




Model No: FT-15

CAUTION

1. Read the instructions on the manual carefully before using for the first time.
2. Before connecting to the power source, check if the voltage specified on the appliance corresponds with the voltage at your home.
3. DO NOT put the appliance or the plug in water or any other liquid. However, if the appliance did contact with liquid, unplug the appliance immediately and have it checked by a qualified technician before using it again.
4. Never put objects into the grill when the fan is connected to its power source.
5. Keep an eye on children while the fan is operating. Stay out of reach for children and do not allow them to play with the fan.
6. It is the best not be exposed to a continuous cold air stream for a long period of time.(esp. children and elders)
7. DO NOT use the fan in very hot or humid environments, such as bathrooms.
8. Keep the fan away from lace curtains, plants, etc.
9. DO NOT connect the appliance to its power source until completely assembled and adjusted.
10. DO NOT use if the power cord or the appliance is damaged, it must be repaired by an authorized service representative as special tool and or parts are required.
11. Keep the cord away from traffic area or where it can be stumbled over.
12. Indoor use only.
13. The appliance is not intended for use by persons (including children) with reduced physical, sensory or mental capabilities, or lack of experience and knowledge, unless they have been given supervision or instruction concerning the use of the appliance by a person responsible for their safety.

STRUCTURE



- 1.FRONT PROTECTIVE FRAME 2.ROTOR BLADE 3.REAR PROTECTIVE FRAME
4.HANDLE 5.SPEED CONTROL SWITCH 0/1/2 6.KNURL BOLT 7.BASE

ASSEMBLY

1. Position the front grill against the rear grill so that the holes in the rims that accept the small nut and bolt are in line.
2. Fully tighten the knurl bolt to fix the base.

OPERATING INSTRUCTIONS

1. Connect the power plug to a suitable outlet.
2. Select the desired speed by pressing the switch 0/I/II.
0 – Device Off
I – Low Speed
II – High Speed
3. The incline of the ventilator head can be adjusted by tilting it forward or backward. The ventilator head can then be locked into position, which is indicated by an audible click.

Maintenance

1. Before cleaning turn the fan off and unplug from the power supply.
2. To clean the fan use a soft cloth to wipe off any dust. If the fan is very dirty use a damp cloth and wipe dry. Do not use any cleaning detergents, sprays or other chemicals, as they will damage the fan.
3. Store the fan in the original packing in a ventilated dry area.
4. The motor bearings are permanently sealed and do not require additional lubrication.
5. Before cleaning turn the fan off and unplug from the power supply.
6. To clean the fan use a soft cloth to wipe off any dust. If the fan is very dirty use a damp cloth and wipe dry. Do not use any cleaning detergents, sprays or other chemicals, as they will damage the fan.
7. Store the fan in the original packing in a ventilated dry area.
8. The motor bearings are permanently sealed and do not require additional lubrication.

TECHNICAL DETAILS

Model No. : FT-15

Power consumption: 17W

Main Voltage: 220-240V~50Hz



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

This mark on a product and/or accompanying documents indicates that when it is to be disposed of, it must be treated as Waste Electrical & Electronic Equipment (WEEE).

Any WEEE marked waste products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used.



Premier Farnell Ltd

For any enquiries regarding the product, please visit www.cpc.co.uk or call 08447 88 00 88