


# Hisense

## NEXT GENERATION 4K U LTRA HD TV



- 55" SMART UHD 4K LED TV
- 4K Upscaling
- Freeview HD & Freesat HD
- PVR (Personal Video Recorder) Ready
- USB Digital Media Player
- Wi-Fi
- Internet Browser
- HDMI 2.0, HEVC, USB 3.0
- Smart TV Apps (Inc. Netflix, BBC iPlayer\* and Amazon Instant Video)\*

\*BBC iPlayer Due End of September, Amazon Instant Video Due End Of December



# LTDN55K321UWTSEU

Panel Performance	
Aspect Ratio	16:9
Diagonal Screen Size	55"/138cm
Panel Resolution	Ultra HD 3840x2160
Typical Viewing Angle (H/V)	85°/85°
Response Time (grey to grey)	6.5ms
Refresh Rate SMR	800Hz
Improving Engines	
Processor	Quad Core
4K Upscaling	Yes
Decoder	HEVC (H.265), VP9
MEMC	Yes
Sound	
Dolby Technology	MS10
Output Power Consumption	2x10W
NICAM / A2 Stereo	NICAM Stereo
User Equalizer	Yes
Convenience	
Multi-Language OSD	Yes
Hotel TV	Yes
PVR	Yes
Time Shift	Yes
Internet Application	
Wireless LAN	Wifi built-in /LAN
Apps	Yes
Web browser	Yes
Internet Ready	Yes
Anyview Cast	Yes
Anyview Stream	Yes
Media Player	Yes
Reception	
Digital Reception(DVB)	DVB-T2/C/S2
Common Interface (CI)	Yes
Astra LCN	Yes
Connecting Interface	
HDMI Input (1.4)	4 (2xHDMI 2.0)
USB (USB2.0)	3 (1xUSB3.0)
S/PDIF Output	1
Audio (L/R) Input	1
Headphone Output	1
Composite (AV) Input	1
Component YPb(Cb)/Pr(Cr)	1
Input	1
SCART	1
Ethernet RJ45 port	Yes

Eco & Power supply	
Power Supply	220V-240V 50Hz
Energy Efficiency Class	A
Standby Consumption	≤0.5w
Power off	0W
Power Consumption (W)	180
Weight & Dimensions	
Net Weight/Gross Weight (Kg)	17.3/22
Package (Horizontal/Vertical)	Vertical
Out Package Size (LxDxH) (mm)	1371x177x858
Net Size With Base (LxDxH) (mm)	1239x262x771
Net Size No Base(LxDxH) (mm)	1239x83x717
EAN	6942147428139
Accessories	
Stand	Yes
VESA Wall Mount (mm)	200x200
Remote control	Yes
Batteries	AAAx2
DMP formats	
Container Format	AVI, WMV, ASF, MP4, MKV, PS, TS, RM, OGG, FLV, VOB, OGM, FLV, MPG, MPEG
Audio	.FLAC .MP2 .MP3 .OGG .WAV .WMA
Picture	.JPG/ JPEG .BMP .PNG .GIF