

cello

Product Model:T1145P

ID Pictures



System Physical Standard Configuration:

Type	Details	Descriptions
Product Form	Dimensions	260mm x 155mm x 12.4mm
LCD Panel	Screen Size	10.1" 16:9
	Screen Resolution	1024*600 TN
Touch Panel	Touch Module	Capacitive
	Multitouch	5 point
Battery	Type	Lithium-ion polymer battery
	Capacity	3.7V/5000mAh

System hardware configuration:

Type	Details	Descriptions
CPU	Type	MT8127,Quad core ,Cortex -A7
	Speed	1.3GHz
GPU	Type	Mali-450 MP4
	Photo Viewer	JPG, GIF, BMP, PNG
Multi-media (Hardware decoding)	Video Format	AVI,3GP,MP4 , MKV,RMVB
	Audio Format	MP3,OGG,WAV,AAC,FLAC
RAM		1GB
ROM Flash		16GB
Camera	Front Facing	0.3MP
	Rear Facing	2.0MP
Speaker	Built-in	8Ω/1W speaker
MIC	Built-in	Yes
G-sensor	Built-in	Gravity acceleration sensor
GPS	Built-in	Yes
Bluetooth	Built-in	BT4.0
WIFI	Built-in	802.11b/g/n
FM	Built-in	Yes
3G	External	USB 3G Dongle

Interface Configuration:

Type	Details	Descriptions
Memory card socket	External memory	MicroSD Card, up to 32GB
SIM Card Socket	SIM Card	N/A
USB interface	Data transfer supportive	USB 2.0 (Micro USB)
Headphone jack	Music output	φ 3.5mm standard headphone jack
DC connector	Power	φ 2.5mm DC jack
HDMI interface	Video output	Mini HDMI
Keys	Tack Switch	POWER/VOL+/VOL-
Keyboard	Input device	Wired Supportive
Mouse	Input device	Wired Supportive

Software Configuration:

Type	Details	Descriptions
Operating System	Operating system version	Android 5.1
	Language	Multi-language supportive

Necessary Accessories:

Type	Details	Descriptions
Power adaptor	Standard Configuration	5V/2A
USB data cable	Standard Configuration	Connect to PC

USB patch cord	Standard Configuration	OTG to HOST
----------------	------------------------	-------------