

## 3M™ Wrist Strap – Adjustable Fabric

This wrist strap set features a fully adjustable, elastic wrist band and 6 or 12 ft coiled cord. The band provides 360 degree conductivity around the wrist for maximum skin contact. The retractable coil cord connects to the wrist band via a 4 mm post snap and contains a 1 megohm resistor. Includes alligator clip. UL listed.



3M™ Wrist Strap, Adjustable Fabric, with 3M™ Coiled Cord

**WARNING:**  
All 3M Wrist Straps should not be used in areas where the individual may come in contact with electrical circuitry exceeding 250 volts.

### Specifications - Band

Fabric	Elastic nylon
Resistance	< 500 ohms
Contact	360 degrees around wrist
Color	Light blue with white edges
Snap	4mm (1/8") machined post
Snap Release	> 3 lbs.
Back Plate	Stainless steel

### Specifications - Cord

Length	6 or 12 feet, extended
Resistance	1 megohm
Flex life	> 16,000 flexes
Color	Black
Markings	UL
Banana Plug	Spinning
Snap	4mm

### Part Numbers 4mm (1/8") snap

WBB-AFWS	Adjustable Fabric Wrist band
WBB-AFWS61M	Adjustable Fabric Wrist band and 6 ft cord
WBB-AFWS121M	Adjustable Fabric Wrist band and 12 ft cord
CC61M	6 ft cord
CC121M	12 ft cord

Meets the requirements of ANSI/ESD S-20.20 -2007, EIA 625.



## 3M™ Wrist Strap – Adjustable Fabric

3M is a trademark of 3M Company.

### Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for one year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



### Electronics Materials Solutions Division Static Control Products

926 JR Industrial Drive  
Sanford, NC 27332-9733  
Toll-Free: 866-722-3736  
International: 919-718-0000  
Email: [3mstaticinfo@mmm.com](mailto:3mstaticinfo@mmm.com)  
[www.3mstatic.com](http://www.3mstatic.com)



Please recycle. Printed in USA.  
© 3M 2014. All rights reserved.  
78-9102-1670-0 JHA