

## Series 3 DC311NBS

### Wireless plug-in doorbell with push button – White

Simple, reliable and hassle-free, the Honeywell DC311NBS plug-in doorbell will never need new batteries. Pre-linked and ready to go out of the box, with a reliable wireless connection and great sound quality, you know you'll never miss a visitor again..



#### Pack

1 x Wireless  
Declaration

button, 1 x CR2032 (3V) Battery, 1 x Quick Start Guide, 1 x Safety & Guarantee, 1 x


#### Key F

**Compact**  
throughout

Doorbells benefit from digitally enhanced, crystal clear sound that carries well -leading sound quality into some deceptively small packages!

**Easy To Install**  
installation and  
guarantee.

Pre-linked and ready to install straight out of the box, with optional screw-free  
mount so you can be set up in minutes. All this is backed up by our 2 year product



## Specification:

### Wireless Plug-in Doorbell

Colour	White
Wall mounted option	No
Frequency	868Mhz
Wireless Range (m)*	150
Range Extender	No
Audible Range (Volume)	60m (80dB)
Melodies	4
Sound	Internal Siren
Power Specification	100-240V 50-60Hz 300mA
USB Charging	No
Dimensions (mm) / Weight (g)	110 (h) x 70 (w) x 64 (d) / 184 (g)

### Wireless Push Button

Colour	White
Wall mounted option	Yes
Frequency	868Mhz
Wireless Range (m)*	200
Low Battery Indicator	Yes
Push Button Design	Portrait
Confidence Light	Yes
Battery Specification	1 x CR2032 (3V)
Battery Life (Years)	2
IP Rating	IP55
Name Plate	No
Dimensions (mm) / Weight (g)	30 (h) x 70 (w) x 16 (d) / 23.5 (g)
Fixings	Brackets / Screws / Rawl Plugs

### Pack

EAN Code	5004100965363
Pack Dimensions (mm) / Weight (g)	216 (h) x 150 (w) x 83 (d) / 370 (g)
Standard Pack Quantity	4

\* Measured in open field conditions, walls, ceilings and metal structures will reduce the maximum range.