

60279

Miniature Circuit Breaker Multi 9 (C60), 15A, 3-Pole, 240 Vac, Line: Ring Tongue



by Schneider Electric

List Price \$378.00 USD

Availability **Non-Stock Item: This item is not normally stocked in our distribution facility.**

Technical Characteristics

Ampere Rating	15A
General Application	Short circuit and overcurrent protection
For Use With	OEM Panels and Enclosures
Voltage Rating	240VAC
Circuit Breaker Type	Standard
Terminal Type	Line: Ring Tongue - Load: Ring Tongue
HACR Rated	Yes
Mounting Type	Flush, Surface or DIN Rail (35mm)
Weight	15.50 Ounces
Approvals	UL489 Listed - CSA 22.2 #5.1 Certified - IEC Rated 60947-2
Number of Poles	3-Pole
Enclosure Rating	IP40
Marketing Trade Name	Multi 9
Short Circuit Current Rating	10kA@240VAC
Type	C60N
Depth	3.00 Inches (76mm)
Height	4.86 Inches (124mm)
Trip Curve	C Curve - Magnetic operates between 7 to 10 times
Width	2.13 Inches (54mm)

Shipping and Ordering

Category	00915 -
Discount Schedule	DE2
GTIN	00785901209683
Package Quantity	1
Weight	0.95 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 01/05/2013 00:35:05