

List Price \$458.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

Fuse Type	Non-Fusible
Horsepower Rating	30HP@240VAC - 60HP@480VAC - 75HP@600VAC
Maximum Voltage Rating	600VAC
Mounting Type	Rail or Panel
Number of Poles	3-Pole
Shaft Type	10mm x 10mm
Terminal Type	Lugs (Built In)
Type	LK3
Depth	3.88 Inches
Height	5.88 Inches
Ampere Rating	100A
Approvals	UL Listed File: E191104 CCN WP2X - CSA Certified File: LR703149 Class 4652 04 - CE Marked
Width	6.69 Inches

Shipping and Ordering

Category	22640 - Disconnect Switches, IEC, Type GS1 & LK3
Discount Schedule	I11
GTIN	00785901179924
Package Quantity	1
Weight	4.07 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	TN

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.