

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191990008**
Status: **Active**
Overview: [Splices](#)
Description: Avikrimp™ Window Butt Connector for 18-22 AWG Wire, Mylar Tape Carrier

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-015 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Splices
 Series 19199
 Comments Mil Spec M7928/5-3
 Crimp Quality Equipment Yes
 Mil-Spec M7928/5-3
 Overview [Splices](#)
 Product Name Avikrimp™, Butt - Window
 UPC 800753046818

Physical

Barrel Type Closed
 Color - Resin Red
 Insulation Nylon (PA)
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 1.194/g
 Packaging Type Adhesive Tape on Reel
 Temperature Range - Operating -55°C to +105°C
 Wire Insulation Diameter 3.56mm max.
 Wire Size AWG 18, 20, 22
 Wire Size mm² 0.25-1.50

Electrical

Voltage - Maximum 300V

Material Info

Old Part Number WA-840T

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-015
 Sales Drawing SD-19199-003



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

19199 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	0192880043
Mini-Mac™ Applicator Air Feed-Mylar Tape	0638859100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION