



Mallory Sonalert Products, Inc.

Part #:

SBT12M0PC

Sales Outline Drawing

Revision:

B


Specifications:

Capable of meeting Medical Spec IEC60601-1-1-8

Sound Level Category:	Loud
Mode of Operation:	Continuous
Voltage Rating:	9 to 12 VDC
Frequency:	150 to 4000 Hz
Loudness @ 10cm:	85 to 95 dB(A) Typ.
Average Current Draw:	<25mA Typ.
l _{pk} Current*:	75mA
Housing Material:	ABS 777D Plastic Resin, Black
Storage Temperature:	-40° to +85° C
Operating Temperature:	-30° to +65° C
Weight Typical:	0.6 oz (17g)
Options:	Please contact factory.

Dimensions: Inches (mm)

ROHS Compliant



*l_{pk} = Instantaneous Peak