



Mallory Sonalert Products, Inc.

Part #:

SBT200PC

Sales Outline Drawing

Revision:

A

Specifications:

Medical Spec IEC60601-1-1-8

Capacitance (pF):	70,000 ± 30% at 120 Hz
Rated Voltage (Vp-p):	5, 30 Max
Current Draw:	1.5 mA at rated voltage
Recommended Drive Frequency:	200 Hz
Loudness @ 10 CM:	85 to 95 dB(A) Typ.
Harmonics Present:	Minimum of 4 peaks within ±15dB from 1-4kHz
Housing Material:	ABS 777D Plastic Resin, Black
Lead Pin:	Tin Plated Brass
Storage Temperature:	-40° to +85° C
Operating Temperature:	-30° to +65° C
Weight (Typical):	0.56 oz (16g)
Options:	Please contact factory.

Dimensions: mm

ROHS Compliant

