

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0561349100](#)
Status: **Active**
Overview: MicroClasp™ Wire-to-Board System
Description: 2.00mm Pitch Crimp Terminal 56134, Female, 22-28 AWG, Bag, Copper Alloy, for 51242/51353/51382/500915 Housings

Documents:

3D Model	Product Specification PS-51353-003 (PDF)
Drawing (PDF)	Product Specification PS-51353-012 (PDF)
Product Specification PS-500637-001 (PDF)	Product Specification PS-51382-004 (PDF)
Product Specification PS-500730-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-51242-002 (PDF)	

General

Product Family	Crimp Terminals
Series	56134
Application	Signal
Crimp Quality Equipment	Yes
MolexKits	Yes
Overview	MicroClasp™ Wire-to-Board System
Product Name	MicroClasp™
UPC	756054317778


Physical

Gender	Female
Material - Metal	Copper-Nickel-Silicon
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	36.000/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.70mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Product Specification	PS-500637-001, PS-500730-001, PS-51242-002, PS-51353-003, PS-51353-012, PS-51382-004, RPS-500637-001, RPS-500637-002, RPS-500730-001, RPS-501844-001, RPS-51216-012, RPS-51242-004, RPS-51242-005, RPS-51242-006, RPS-51242-007, RPS-51353-005, RPS-51353-008, RPS-51353-009, RPS-51353-010, RPS-51353-014, RPS-51353-016, RPS-51353-017, RPS-51353-018, RPS-51353-019, RPS-51353-020, RPS-51353-022, RPS-51353-024, RPS-51353-025, RPS-51353-026, RPS-51353-027, RPS-51353-031, RPS-51353-033, RPS-51353-034, RPS-51353-036, RPS-51353-037, RPS-51382-006, RPS-51382-007, RPS-51382-008, RPS-51382-009, RPS-51382-010, RPS-51382-011, RPS-51382-012, RPS-51382-013, RPS-51382-014, RPS-51382-015, RPS-51382-018
Sales Drawing	SD-56134-005



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

56134 Series

Use With

500915 Dual Row Crimp Housing, 51242 Dual Row Crimp Housing, 51353 Dual Row Crimp Housing, 51382 Single Row Crimp Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	0638132700
Hand Crimp Tool	0638116300
Insertion Tool	0011020022

Japan

Description	Product #
-------------	-----------

This document was generated on 09/09/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION