

Dual Full-Motion Flex Arm Desk Clamp for 13" to 27" Flat-Screen Displays

MODEL NUMBER: DDR1327DCS



Highlights

- Increases available desk/table space in office workstation applications
- Dual mounts fit most flat-panel displays from 13" to 27"
- Convenient one-touch display adjustment for easy view optimization and improved ergonomics
- Wide range of motion with -80° to +90° tilt, 180° swivel and 360° rotation capability
- Each mount supports up to 22 lbs.

Package Includes

- DDR1327DCS Dual Full-Motion Flex Arm Desk Clamp for 13" to 27" Flat-Screen Displays
- Mounting Hardware
- Owner's Manual

Description

Tripp Lite's VESA-compliant DDR1327DCS Flex Arm Dual Desk Clamp frees up valuable space in your workstation. The unique flexible design offers an exceptional range of motion. Dual swivel arms are independently height adjustable to allow complete flexibility to position monitors to accommodate your visual needs. Increase workday productivity with flexible arms that allow monitors to be placed back to back for use by more than one person. You can bring the screen closer when you need or move out of the way when you don't and space between the monitors is also fully adjustable. It features convenient one-touch display adjustment with tilt, swivel and rotation capabilities and fits most 13- to 27-inch flat-panel displays. Its durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any decor. It comes with all necessary mounting hardware, and each mount supports weights of up to 22 lbs.

Features

- VESA-compliant Flex Arm Dual Flat-Screen Desk Clamp frees up valuable space in your workstation and increases workday productivity with flexible arms that allow monitors to be placed back to back for use by more than one person
- Unique flexible design with swivel arms that are independently height adjustable offers an exceptional range of motion
- Convenient one-touch display adjustment with tilt, swivel and rotation capabilities and fits most 13- to 27-inch flat-panel displays
- Durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any decor
- Includes all necessary mounting hardware, and each mount supports weights of up to 22 lbs.

Specifications

PHYSICAL	
Mounting Location	Desk Clamp
Unit Dimensions (hwd / in.)	12.52 x 33.86 x 4.45
Unit Dimensions (hwd / cm)	31.80 x 86.0 x 11.30



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Weight (lbs.)	6.56
Unit Weight (kg)	2.98
Material of Construction	Steel
Color	Black
Screen Size Compatibility (in.)	13 - 27
Screen Size Compatibility (cm)	33.02 - 68.58
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Degrees of Motion	-80/+90 Tilt; 180 swivel; 360 rotate
Maximum Weight Capacity (lbs.)	22
Maximum Weight Capacity (kg)	9.98
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	Yes
WARRANTY	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>