

## Full-Motion Wall-Mount w/ Arms for 17" to 42" Flat-Screen Displays

MODEL NUMBER: DWM1742MA



### Highlights

- **REPLACES MODEL DWM1737MA**
- Can be used to increase available desk/table space in office applications
- Fits most flat-panel displays from 17" to 42"
- Convenient one-touch display adjustment for easy view optimization
- Wide range of motion with -15° to +15° tilt, 180° swivel and -3° to +3° screen level adjustment capability
- Supports up to 77 lbs.
- 5-year warranty

### Package Includes

- DWM1742MA Full-Motion Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual

### Description

Tripp Lite's VESA-compliant DWM1742MA Full-Motion Flat-Screen Wall Mount offers full-motion articulation and can free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation. Its sleek design features convenient one-touch display adjustment with tilt and swivel capabilities and fits most 17- to 42-inch flat-panel displays. Its durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any décor. It comes with all necessary mounting hardware and supports weights of up to 77 lb. For peace of mind, the DWM1742MA comes backed by a 5-year warranty.

## Specifications

PHYSICAL	
Mounting Location	Wall
Unit Weight (lbs.)	7.88
Unit Weight (kg)	3.57
Color	Black
Screen Size Compatibility (in.)	17 - 42
Screen Size Compatibility (cm)	43.18 - 106.68
VESA Pattern (mm)	75x75; 100x100; 200x100; 200x200
Motion	Full
Degrees of Motion	-15/+15 Tilt; 180 Swivel; -3/+3 Level Adjustment
Min/Max Arm Extension (in.)	2.21 min to 20.08 max
Min/Max Arm Extension (cm)	5.6 min to 51 max



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Maximum Weight Capacity (lbs.)	77
Maximum Weight Capacity (kg)	35
<b>FEATURES &amp; SPECIFICATIONS</b>	
Tools Necessary	Yes
Cord Management	No
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>